

GV7RE150

motor circuit breaker GV7-RE - 3 poles 3d -
90...150A - thermomagnetic trip unit



Main

Commercial Status	Commercialised
Range of product	GV7R
Device short name	Thermal magnetic circuit breaker
Circuit breaker application	Motor protection
Poles description	3P
Network type	AC
Control type	Rocker lever
Thermal protection adjustment range	90...150 A conforming to IEC 60947-4-1
Suitability for isolation	Yes conforming to IEC 60947-1 § 7-1-6
Utilisation category	Category A conforming to IEC 60947-2 AC-3 conforming to IEC 60947-4-1
Connections - terminals	Power circuit: screw clamp terminal

Complementary

Network frequency	50/60 Hz
Mounting mode	Fixed
Mounting support	Plate Rail
Mounting position	Horizontal Vertical
Motor power kW	90 kW at 660...690 V AC 50/60 Hz 90 kW at 500 V AC 50/60 Hz 75 kW at 500 V AC 50/60 Hz 75 kW at 400...415 V AC 50/60 Hz 55 kW at 400...415 V AC 50/60 Hz 110 kW at 660...690 V AC 50/60 Hz
[In] rated current	150 A
Phase failure sensitivity	Yes conforming to IEC 60947-4-1 § 7-2-1-5-2
[Ue] rated operational voltage	600 V AC 50/60 Hz conforming to CSA C22.2 No 14 690 V AC 50/60 Hz conforming to IEC 60947-2 600 V AC 50/60 Hz conforming to UL 508
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 750 V conforming to IEC 60947-2 600 V conforming to UL 508
[Ith] conventional free air thermal current	150 A conforming to IEC 60947-4-1
Network frequency	50/60 Hz conforming to UL 50/60 Hz conforming to IEC 60947-4-1 50/60 Hz conforming to CSA
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
Power dissipation per pole	8.7 W
Mechanical durability	40000 cycles
Electrical durability	40000 cycles on AC-3 at 440 V In/2 20000 cycles on AC-3 at 440 V In
Maximum number of switchings	25 cyc/h
Rated duty	Continuous conforming to IEC 60947-4-1
Connection pitch	45 mm with spreaders 35 mm without spreaders
Tightening torque	15 N.m - on screw clamp terminal
Type of lugs	Lugs - width: <= 25 mm - distance hole to end: <= 10 - thickness: <= 6 mm - screw: M8 Bars - width: <= 25 mm - height: 20 mm - distance hole to end: <= 10 - thickness: <= 6 mm - screw: M8

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Breaking capacity	Icu 85 kA at 230...240 V AC 50/60 Hz conforming to IEC 60947-2 Icu 8 kA at 690 V AC 50/60 Hz conforming to IEC 60947-2 Icu 35 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 Icu 35 kA at 400...415 V AC 50/60 Hz conforming to IEC 60947-2 Icu 30 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	100 % at 690 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 440 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 400...415 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 230...240 V AC 50/60 Hz conforming to IEC 60947-2
Height	161 mm
Width	105 mm
Depth	111 mm
Product weight	2.02 kg

Environment

Standards	EN 60947-1 EN 60947-2 EN 60947-4-1 IEC 60947-1 IEC 60947-2 IEC 60947-4-1 NF C 63-120 NF C 63-650 NF C 79-130 VDE 0113 VDE 0660
Product certifications	CCC DNV UL
Protective treatment	TC
IP degree of protection	IP405 with terminal shrouds conforming to IEC 60529 IP405 open mounted conforming to IEC 60529
Shock resistance	15 gn 20 ms conforming to IEC 60068-2-27
Vibration resistance	2.5 gn 25 Hz conforming to IEC 60068-2-6
Ambient air temperature for operation	-25...70 °C open mounted
Ambient air temperature for storage	-55...95 °C
Fire resistance	960 °C conforming to IEC 60695-2-1
Operating altitude	<= 2000 m
Resistance to mechanical impact	0.5 J

Contractual warranty

Period	18 months
--------	-----------