


D

C

B

A



LC CONN. MARK	LC CONN. MARK
A	B
B	A


NOTES:

- 1 ATTENUATION ≤ 0.3 dB, MEASURED AT 1310 nm
ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2 RETURN LOSS ≥ 45 dB, IN MATED CONDITION
AGAINST REFERENCE CONNECTOR AT 1310 nm
- 3 TUNED CONNECTORS
- 4 CABLE INFORMATION:
 - CORE DIAMETER: 9/125 μm
 - OUTER JACKET DIAMETER: 1.8x3.6 mm
 - OUTER JACKET COLOUR: YELLOW
 - OUTER JACKET MATERIAL: LSZH
- 5

BLANK LABEL
- 6

INFORMATION ON LABEL
 - BARCODE
 - UNIQUE SERIAL NUMBER
 - TYCO ELECTRONICS PART NUMBER & ORDER NUMBER
 - ATTENUATION & RETURN LOSS AT 1310 nm

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061308-Y	XY.0

6	FOAC INFORMATION LABEL			3
2	LC DUPLEX CONNECTOR, SINGLE MODE, BLUE			2
L	FOCAB 1.8MZ 9/125, YELLOW, LSZH			1
Qty	Description			Item
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. COOLEN 16OCT2009 CHK A. HENGELMOLEN 16OCT2009 APVD A. HENGELMOLEN 16OCT2009 PRODUCT SPEC — APPLICATION SPEC — WEIGHT —	 Tyco Electronics Corporation 's-Hertogenbosch, Nederland NAME FIBER OPTIC LEAD 1.8MZ LC/DPX — LC/DPX SINGLE MODE 9/125 SIZE A2 CAGE CODE 00779 DRAWING NO C=2061308 RESTRICTED TO —
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH —		
MATERIAL —		CUSTOMER DRAWING		SCALE NTS SHEET 1 of 1 REV A