




Price\* : 33.77 GBP



## Main

Range	Spacial
Product name	Spacial SBM
Device application	Multi-purpose
Product or component type	Extension box
Device short name	SBM
Enclosure nominal height	300 mm
Enclosure nominal width	500 mm
Enclosure nominal depth	80 mm
Device composition	4 x screw 1 x body
Body type	Single piece body folded and welded
Cover fixing	Half turn metal screw
Lock type	Inside the enclosure : PZ2 screwdriver captive screw

## Complementary

Material	Sheet steel
Surface finish	Polyester powder
Colour	Grey ( RAL 7035 )
IP degree of protection	IP66 IEC 60529 for 1 device
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for storage	-35...60 °C
Ambient air temperature for operation	-35...80 °C
Product weight	2.688 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 1241 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations