

Product Information

2944UAP125R26-28S45

EAN 4031582302547

Swivel castor with central, total or directional lock, Steel frame, yellow zinc plated, precision ball bearing in both wheels, covered swivel head welded to the steel frame, housing with synthetic cover.

Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing, stem with cam hole for profile bars

Option:

This castor is also in electric conductive version available. (grey non-marking). Please replace UAP with XSX when ordering..



Wheel diameter	125 mm
Width of Tread	60 mm
Bolt-Ø	28 mm
Bolt lenght	96 mm
Offset	37.5 mm
Swivel Interference	200 mm
Overall height	150 mm
Temperature	- 30 / + 80 °C
Standard	EN 12531
Weight	1.419 kg
Dynamic Load capacity	125 kg
Static Load capacity	250 kg
Hardness of tread	D 40 Shore

Versions:

