

DO NOT SCALE
DIMENSIONS IN

METRIC

3rd ANGLE PROJECTION

NOTES

- 1 MATERIAL: HOUSING: TERMOPLASTICO S/ FIBRA DE VIDRO V-0 COR: PRETO
CONTACT: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITHOUT GLASS FIBER V-0 COLOR: BLACK
CONTACT: PHOSPHOROUS BRONZE
- 2 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO NR. COR: NATURAL
CONTACT: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER NR. COLOR: NATURAL
CONTACT: PHOSPHOROUS BRONZE
- 3 0,38 µm. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL
0,38 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING
- 4 0,76 µm. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL
0,76 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING
- 5 1,27 µm. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL
1,27 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING
- 6 ESTANHO SOBRE NIQUEL
TIN UNDER NICKEL
- 7 PONTO DE CONTATO E/ MEDIÇÃO DA CAMADA DE OURO
CONTACT POINT FOR GOLD PLATING MEASUREMENT
- 8 ACETA PINO QUADRADO 0,64 x 0,64 OU REDONDO Ø 0,64
ALLOW SQUARE PIN 0,64 x 0,64 OR ROUND Ø 0,64
- 9 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO COR VERMELHO, V-2
CONTACT: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER COLOR RED; V-2
CONTACT: PHOSPHOROUS BRONZE


	3	10	L	2 - 880584	- 1
11 OBSOLETE	6	9			9
11 OBSOLETE	6				8
	5				- 7
11 OBSOLETE	4				6
	3	2			- 5
	6				- 4
11 OBSOLETE	5				- 3
	4				- 2
	3	1	K1	880584	- 1

OTHER TREATMENT	FINISH	MATERIAL	PART REV.	PART NUMBER
CUSTOMER DWG for REFERENCE ONLY				
TOLERANCES UNLESS OTHERWISE STATED DEC. ± 0,3 ANGLES ± 1°		INS. DIA. RANGE //	WIRE RANGE //	SCALE //
DR. <i>Paulo</i> 01/01/84		TE Connectivity		
CHK. <i>H</i> 10 JUN 84		DESCRIPTION AMP SHUNT CONNECTOR ASS'Y		
DE.				
L3 REVISED PER ECO-11-005139	RK HMR 28MAR11			
REVISION	RECORD	OR	CHK	DATE
APP. <i>[Signature]</i>		A3 C 880584		
		SHEET 10/2		

C 880584

10 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO V-2 COR: VERDE
CONTATO: BROZE FOSFOROSO
MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER V-2 COLOR: GREEN
CONTACT: PHOSPHOROUS BRONZE

11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



11 OBSOLETE	6			1	8
	5			1	7
	4			1	6
	3		2	1	5
	6			1	4
	5			1	3
11 OBSOLETE	4			1	2
	3		1	K1	1 - 880584 - 1

OTHER TREATMENT	FINISH	MATERIAL	PART REV.	PART NUMBER
CUSTOMER DWG for REFERENCE ONLY				
TOLERANCES UNLESS OTHERWISE STATED DEC. ± 0,5 ANGLES ± 1°		INS. DIA. RANGE	WIRE RANGE	SCALE
DR. <i>Exlor</i> CHK. <i>NW</i> DATE 09-MAR-87		TE Connectivity		
DESCRIPTION AMP SHUNT CONNECTOR ASS'Y		SHEET 2 of 2		
DWG NO A3 C 880584				