


Chargers for Li-Ion batteries - switch mode

tech spec

2241 LI - exchangeable / utskiftbare AC plugs

- 3-step charge control with current detection as charge termination
- Universal input voltage (90-264 VAC)
- Charging 1-7 battery cells
- Order mains cord separately
- Waterproof (IP67) version available
- Exchangable AC and DC plugs
- Custom specifications on request
- Approvals:
 - Medically certified EN60601 3ed
 - UL-approved
 - For updates: see www.mascot.no
- 3-trinns ladekontroll med strømdeleksjon som ladestopp
- Universal inngangsspenning (90-264 VAC)
- Opplading av 1-7 battericeller
- Nettledning best. separat
- Vanntett (IP67) versjon kan leveres
- Utskiftbare AC og DC plugger
- Tilpasninger leveres på forespørsel
- Godkjenninger:
 - Medisinsk sertifisert EN 60601 3ed
 - UL-godkjent
 - For oppdat.: se www.mascot.no



2241

2240

Technical specifications Tekniske data

Input voltage:	Inngangsspenning:	90-264 VAC
Line frequency:	Frekvensområde:	47 – 63Hz
Switch frequency, approx.:	Svitsjefrekvens ca.:	40kHz
Leakage current from battery with mains switched off:	Strømtrekk fra batteri ved frakoblet nett:	≈ 0
Temperature range	Temperaturområde	
• operating:	• drift:	-25 °C - +40 °C
• storage:	• lagring:	-25 °C - +85 °C
Ripple:	Rippel:	< 100 mV p-p
Protection:	Beskyttelse.:	Protected against reversed polarity and short circuit proof
		Polvendings- og kortslutningssikker
Insulation class:	Isolasjonsklasse:	II
Insulation voltage	Isolasjonsspenning	
Primary – secondary:	Primær - sekundær:	4000VAC / 5640VDC
Electrical safety:	Elektrisk sikkerhet:	EN 60601-1 3ed, EN 60950, EN 60335-2-29,
EMC standards	EMC standarder	
• Medical:	• Medisinsk:	EN 60601-1-2
• Emission:	• Emisjon:	EN 61000-6-3
• Immunity:	• Immunitet:	EN 61000-6-1
Reliability (MIL-HDBK-217F):	Pålitelighet (MIL-HDBK-217F):	MTBF > 250.000h at 30°C and full load
Output terminals:	Utgangsterminaler:	Cord with/without plug
		Sekundærledning med / uten plugg
IP-code:	IP-grad:	4X
Dimensions (LxWxH):	Mål (LxBxH):	90 x 45 x 32mm (2240 LI)
Weight:	Vekt:	115g (215g IP67 vers.)

Versions - Versjoner			Charge control - Ladekontroll			
			Step 1	Step 2	Step 3	
Cells	Max. output power (W)	Efficiency 100% at 230V	Charge current (orange)	Charge voltage (orange)	Charge termination I< (green)	Charge start Vbat<
Celler	Max. utg. effekt	Virkningsgrad	Ladestrom	Ladespenning	Ladestopp I< (grønn)	Ladestart Vbat<
1	5,5	58 %	1,3A +5/-7%	4,2V +-0,05V	100mA +-25%	4,05V+0,05-0,15V
2	10,9	72 %	1,3A +5/-7%	8,4V +-0,1V		8,1V+0,1-0,15V
3	15,1	77 %	1,2A +5/-7%	12,6V +-0,1V		12,3V+0,1-0,15V
4	15,1	80 %	0,9A +5/-7%	16,8V +-0,1V		16,4V+0,1-0,15V
5*	14,7	82 %	0,7A +5/-7%	21,0V +-0,1V		20,5V+0,1-0,15V
6*	15,1	82 %	0,6A +5/-7%	25,2V +-0,1V		24,6V+0,1-0,15V
7*	16,4	82 %	0,56A +5/-7%	29,4V +-0,1V		28,7V+0,1-0,15V

* Complies with EN 60601-1 3ed, not UL approved