

## Housing - HC-HV 10/16-KML-79/M1PG21 - 1774157

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Coupling housing, with single locking latch, height 79 mm, with screw connection, 1x Pg21



### Key commercial data

Packing unit	10 pc
GTIN	 4 017918 115470
Weight per Piece (excluding packing)	431.2 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Height	79 mm
Width	43 mm
Length	120 mm
Wrench size, union nut	28 mm
External cable diameter	10 mm ... 19 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-HV10/16
Type	HV10/16
Housing type	Coupling housings
Locking type	With single locking latch
No. of cable outlets	1
Cable exit	Straight

# Housing - HC-HV 10/16-KML-79/M1PG21 - 1774157

## Technical data

### General

Screw connection	with
Type of the screw connection	1x Pg21
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Cable gland material	Nickel-plated brass
Cable seal material	NBR
Material lock	High-grade steel
Material grip body interlock	PA-GF

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

#### Approvals

#### EAC

---

# Housing - HC-HV 10/16-KML-79/M1PG21 - 1774157

## Approvals

Ex Approvals

---

Approvals submitted

---

Approval details

EAC
-----

## Drawings

Dimensioned drawing

