


77 Electronics Diagonal Cutters



DIN ISO 9654




77 01 115
Style 0: round head, with bevel



77 02 115
Style 0: round head, with small bevel



77 12 115
Style 1: round head, with bevel and lead catcher - no uncontrolled loss of cut wire ends



77 12 115



77 22 115
Style 1: round head, without bevel

- ▶ precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- ▶ precision box joint
- ▶ low-friction double spring for gentle and even opening
- ▶ the polish or mirror polish (only finish 2) together with a fine film of oil offer the best possible rust protection - no circuit faults caused by peeling chrome from plated tools
- ▶ cutting edges additionally induction hardened, cutting edge hardness approx. 62 HRC
- ▶ special tool steel, oil-hardened and tempered

Models 77 22 115, 77 42 115, 77 42 130 and 77 52 115:

- ▶ cutting edges hardness approx. 57 HRC

Models 77 21 115:

- ▶ pointed head, without bevel

Models 77 21 130:

- ▶ round head, without bevel



77 32 115
Style 3: pointed head, with small bevel



77 42 115
Style 4: pointed head, without bevel




77 52 115
Style 5: pointed, flat head, with small bevel



77 72 115
Style 7: pointed mini-head, with small bevel



00 20 16



Article-No.	EAN-Code	Style	Head	Handles	Dimensions			Cutting capacities			g
					B	A	D	Ø mm	Ø mm	Ø mm	
77 01 115	018568	0	polished	plastic coated	14.0	11.0	7.5	0.3 - 1.6	1.2	0.5	70
130	018575				18.0	15.0	9.5	0.3 - 2.0	1.5	0.8	110
77 02 115	039334		mirror polished	with two-colour dual component handles	14.0	11.0	7.5	0.3 - 1.6	1.2	0.5	80
130	039341				18.0	15.0	9.5	0.3 - 2.0	1.5	0.8	125
77 11 115	018629	1	polished	plastic coated	14.0	11.0	7.5	0.3 - 1.6	1.2	0.5	70
77 12 115	043768		mirror polished	two-colour dual component handles	14.0	11.0	7.5	0.3 - 1.6	1.2	0.5	80
77 21 115	018650	2	mirror polished	with two-colour dual component handles	14.0	11.0	7.5	0.3 - 1.3	1.0	-	70
130	018667				18.0	15.0	9.5	0.3 - 1.6	1.3	-	115
77 22 115	043782		mirror polished	with two-colour dual component handles	14.0	11.0	7.5	0.3 - 1.3	1.0	-	85
130	040446				18.0	15.0	9.5	0.3 - 2.0	1.5	0.5	120
77 32 115	044307	3	mirror polished	two-colour dual component handles	14.0	11.0	7.5	0.3 - 1.3	1.2	0.5	80
77 42 115	039761	4	mirror polished	with two-colour dual component handles	14.0	11.0	7.5	0.3 - 1.3	1.0	-	85
130	018773				18.0	15.0	9.5	0.3 - 1.6	1.3	-	125
77 52 115	040750	5	mirror polished	two-colour dual component handles	14.0	11.0	7.5	0.3 - 1.0	0.8	0.5	80
77 72 115	040958	7	mirror polished	two-colour dual component handles	10.5	9.5	6.5	0.3 - 0.8	-	-	70