

Enamelled copper wire on mini bobbin **CUL 500/0,75**



Advantages

Insulating varnish basis min. polyurethane, mod. current loading

Degree 1

TJ min. 155 °C

Solderable

Applications

Enamelled copper wire for the production of coils and winding and for general laboratory needs.

Approvals



Enamelled copper wire on mini bobbin **CUL 500/0,75**

| Type | CUL 500/0,75 | Type | CUL 500/0,75 |
|-----------------|--------------|--------------------------|------------------------|
| Electrical data | | 30 Operating data | |
| | | current car. cap. | 1.55 A |
| | | Environment | |
| | | Heat resistance | 155 °C (CL.F) |
| | | insulating varnish | min. Polyurethan, mod. |
| | | Tin-plate | >350 °C |
| | | Measures and weights | |
| | | Wire diameter | 0.75 mm |
| | | Weight | 0.50 kg |
| | | Length m (min.) | 99 |

Subjects to change.