






Technical drawing of a 16-pin connector. The drawing shows a top view of the connector with dimensions and callouts.

Dimensions:

- Overall width: 58,42
- Pin pitch (center-to-center): 2,54
- Pin pitch calculation: $2,54 \times 16 = (40,64)$
- Distance from left edge to first pin: 1,52
- Distance from left edge to last pin: 2,54

Callouts:

- 1) All holes $\varnothing 0,05$
- 1st contact
- Min. $\varnothing 2,8$

09 18 534 7902	3	4,5
09 18 534 6902	2	4,5
09 18 534 5902	0,76 $\mu\text{m Au}$	4,5
09 18 534 7904	3	2,9
09 18 534 6904	2	2,9
09 18 534 5904	0,76 $\mu\text{m Au}$	2,9
Part number	Performance level	a

				Dat.	Name		SEK 18 Male Connector Standard 34 poles Straight solder pins Long locking levers	Maßstab/ Scale 1,5:1	
			Detail.	01/12/99	JB				
34900	28/01/08	LP	Insp.						All Dim. in mm Orig. Size DIN A 3
33451	30/03/06	JMDR	Stand.						
27931	15/06/00	JB	HARTING EURL F-95972 Paris					TB 09 18 534 X90X	Blatt/ Page 1 / 2
26554	01/12/99	JB							
Mod.	Dat.	Name					Sub.		