

LEDVANCE DOWNLIGHT L WT 830

LEDVANCE DOWNLIGHT L | LED downlights



Areas of application

- Compatible with standard suspended ceilings
- Replacement for downlight applications of compact fluorescent lamps
- Corridors
- Foyers
- Lobbies
- Shops

Product benefits

- Excellent energy balance
- Elegant design
- Fast ceiling integration thanks to easy installation system
- Shallow mounting depth

Product features

- Average lifespan: 50,000 h
- Color temperature: 3,000 K (Warm White) or 4,000 K (Neutral White)
- Direct connection to a 220...240 V AC supply
- Recessed ceiling mounting



Technical data


Electrical data

Operating mode	ECG
Nominal wattage	12 W
Nominal voltage	220...240 V
Mains frequency	50...60 Hz

Light technical data

Color temperature	3000 K
Beam angle	80 °
Luminous flux	1050 lm
Light color as per EN 12464-1	Warm white

Dimensions & weight



Product line drawing

Diameter	172.0 mm
Height	72.0 mm

Colors & materials


Body material	Polymer
Product color	Grey
Cover material	Polymer

Temperatures

Ambient temperature range	≤ +25 °C
---------------------------	----------

Product datasheet

Additional product data



LDC typ luminance

Type of cover	Diffuser disc
---------------	---------------

Capabilities

Type of installation	Recessed
Type of connection	cable, 2x 0.75mm ²

Certificates & standards

Protection class	II
------------------	----

Country specific categorizations

Order reference	LDV DOWNLIGHT L
-----------------	-----------------

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.