



⚠ Important Safety Notice ⚠

It is the responsibility of the person installing the electrical equipment to ensure that the installation meets the requirements of the IET wiring regulations and is therefore 'fit for purpose'. Factors such as correct selection of components, cable sizing, protective devices and Earth bonding are all critical and should be checked prior to full testing and power-up. Any other regulations applicable to the equipment being installed such as the Machinery Directive and current health and safety legislation must also be adhered to. Terminals, including factory fitted, should be checked periodically to ensure correct tightness.



Basic circuit diagram



- Ready-to-install equipment for use acc. to the lightning protection zones concept as required in BSEN 62305-4
- Quick and easy installation, premounted with spark-gap-based combined lightning current and surge arrester
- Discharge capacity I_{imp} up to 25 kA (10/350 μ s)
- Co-ordinated Lightning current and surge arrester
- Operating state/fault indication by mark in the inspection window
- Enclosure with transparent cover, degree of protection: IP 65

Technical Data 7869409

SPD according to EN 61643-11 / IEC 61643-11-11	Type 1 / Class I
Energy coordination with terminal equipment	Type 1 + Type 2
Energy coordination with terminal equipment (≤ 5 m)	Type 1 + Type 2 + Type 3
Nominal a.c. voltage (U_N)	230 V
Max. continuous operating a.c. voltage (U_C)	255 V
Lightning impulse current (10/350 μ s) [L+N-PE] (I_{total})	25 kA
Specific energy [L+N-PE] (W/R)	156.25 kJ/ohms
Lightning impulse current (10/350 μ s) [L, N-PE] (I_{imp})	12.5 kA
Specific energy [L,N-PE] (W/R)	39.06 kJ/ohms
Nominal discharge current (8/20 μ s) (I_n)	12.5 / 25 kA
Voltage protection level [L-PE]/[N-PE] (U_p)	$\leq 1.5 / \leq 1.5$ kV
Follow current extinguishing capability a.c. (I_f)	25 kA _{rms}
Follow current limitation/Selectivity	no tripping of a 32 A gL/gG fuse up to 25 kA _{rms} (prosp.)
Response time (t_d)	≤ 100 ns
Max. mains-side overcurrent protection	160 A gL/gG
Temporary overvoltage (TOV) [L-N] (U_T)	440 V / 5 sec.
TOV characteristic	withstand
Operating temperature range (T_u)	-40 °C...+80 °C
Operating state/fault indication	green / red
Number of ports	1
Cross-sectional area (L, N, PE, \oplus) (min.)	1.5 mm ² solid/flexible
Cross-sectional area (L, N, PE, \oplus) (max.)	35 mm ² stranded/25 mm ² flexible
For mounting on	35 mm DIN rails acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Technical data insulating enclosure	--
- Operating temperature range (T_u)	-25°C...+40°C
- Degree of protection	IP 65
- Cover	transparent door
- Colour of enclosure	grey
- Cable entry	8 cable entries
- Capacity	4 modules
- Material	plastic
- Dimensions	Height: 210 x Width: 125 x Depth 100mm
PU	1 pc(s)