

77 22 115


Electronics Diagonal Cutter



- For fine cutting work, e.g. in electronics and fine mechanics
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened
- High-grade special tool steel, forged, multi stage oil-hardened
- Round head, without bevel
- Cutting edge hardness approx. 57 HRC



Article No.	77 22 115
EAN	4003773027973
Head	mirror polished
Handles	with multi-component grips
Style	2
Cutting capacities medium hard wire (diameter) Ø mm	1,0
Cutting capacities soft wire (diameter) Ø mm	0,3 - 1,3
D mm	7,0
B mm	14,0
A mm	11,0
Length mm	115
Net weight g	80



technical change and errors excepted

