

## LATER 4 G/30-V0

Compound based on Polybutylene Terephthalate (PBT).

Glass fibres. UL94 V-0 classified, with halogens, PBB/PBDE free. Product UL certified.

PHYSICAL PROPERTIES - Typical values	STANDARD	VALUE MEASURE UNITS
Density	ISO 1183	1.58 g/cm <sup>3</sup>
<b>Linear shrinkage at moulding - 0.078 in thickness (at 8,700 psi of cavity pressure)</b>		
Longitudinal	ISO 294-4	0.003 ÷ 0.005 in/in
Transversal	ISO 294-4	0.010 ÷ 0.013 in/in
MECHANICAL PROPERTIES - Typical values		
<b>IZOD impact strength (sample 2.5x0.5x0.125 in)</b>		
Notched, at +73°F	ASTM D 256-A	1.80 ft.lb/in
<b>CHARPY impact strength (sample 3.149x0.393x0.157 in)</b>		
Unnotched, at +73°F	ISO 179-1eU	21.03 ft.lb/in <sup>2</sup>
Unnotched, at -4°F	ISO 179-1eU	23.36 ft.lb/in <sup>2</sup>
Notched, at +73°F	ISO 179-1eA	3.27 ft.lb/in <sup>2</sup>
Notched, at -4°F	ISO 179-1eA	2.80 ft.lb/in <sup>2</sup>
<b>Tensile elongation (speed 0.196 in/min)</b>		
At break, 73°F	ISO 527 (1)	2.5 %
At break, 140°F	ISO 527 (1)	3.5 %
At break, 195°F	ISO 527 (1)	6 %
At break, 250°F	ISO 527 (1)	6 %
At break, 300°F	ISO 527 (1)	6 %
<b>Tensile strength (speed 0.196 in/min)</b>		
At break, 73°F	ISO 527 (1)	17,400 psi
At break, 140°F	ISO 527 (1)	12,300 psi
At break, 195°F	ISO 527 (1)	9,400 psi
At break, 250°F	ISO 527 (1)	7,300 psi
At break, 300°F	ISO 527 (1)	5,800 psi
<b>Elastic modulus</b>		
Tensile (speed 0.04 in/min), at 73°F	ISO 527 (1)	1,523 kpsi
Tensile (speed 0.04 in/min), at 140°F	ISO 527 (1)	1,073 kpsi
Tensile (speed 0.04 in/min), at 195°F	ISO 527 (1)	711 kpsi
Tensile (speed 0.04 in/min), at 250°F	ISO 527 (1)	522 kpsi
Tensile (speed 0.04 in/min), at 300°F	ISO 527 (1)	377 kpsi

## LATER 4 G/30-V0

Compound based on Polybutylene Terephthalate (PBT).

Glass fibres. UL94 V-0 classified, with halogens, PBB/PBDE free. Product UL certified.

THERMAL PROPERTIES - Typical values	STANDARD	VALUE	MEASURE UNITS
<b>Coefficient of linear thermal expansion (CLTE)</b>			
+86°C to +212°F (longitudinal)	ASTM D 696	8	µin/(in·°F)
<b>VICAT - Softening point</b>			
11 lb (heating rate 11°F/h)	ISO 306	392	°F
<b>HDT - Heat Deflection Temperature</b>			
66 psi	ISO 75	428	°F
264 psi	ISO 75	374	°F
<b>C.U.T. - Continuous Use Temperature (20,000h)</b>	---	275	°F
<b>FLAMMABILITY - Typical values</b>			
<b>Oxygen Index</b>	ASTM D 2863	28	%
<b>Flammability rating</b>			
0.118 in thickness	UL 94	V-0	rating
0.059 in thickness	UL 94	V-0	rating
0.029 in thickness	UL 94	V-0	rating
<b>GWFI - Glow Wire Flammability Index</b>			
	IEC 695-2-12	GWFI: 960/1.0mm	
	IEC 695-2-12	GWFI: 960/2.0mm	
<b>ELECTRICAL PROPERTIES - Typical values</b>			
<b>CTI - Comparative Tracking Index</b>			
solution A (without surfactant)	IEC 112	250	V

## LATER 4 G/30-V0

Compound based on Polybutylene Terephthalate (PBT).

Glass fibres. UL94 V-0 classified, with halogens, PBB/PBDE free. Product UL certified.

### PREDRYING CONDITIONS

At least 3 hours at 230 ÷ 265°F

These are the suggested conditions to reduce the moisture content to adequate levels. Temperature and drying time are reduced when using vacuum ovens. A particularly wet material may need longer drying time.

### ACTUAL MELT TEMPERATURE

465 ÷ 480°F

The injection machine settings needed to obtain the suggested melt temperature will depend greatly on shot size and machine capacity, as well as other molding parameters such as: injection speed, screw RPM, back pressure, etc. On small machines, running short cycles, it is possible to use higher melt temperatures to improve plastification, fluidity and surface appearance, paying attention to any indication of material degradation.

### MOLD TEMPERATURE

160 ÷ 195°F

The mold temperature suggested above is the actual steel temperature. This can be significantly different from the tool settings, due to the cooling system efficiency and the accuracy of the temperature control on the tool.

### INJECTION SPEED

Medium

The advisable injection speed greatly depends on cavity geometry and injection machine size. The use of high injection speed can improve the surface appearance, but it can also cause outgassing and burn marks due to overheating through shear stress.

### REGRIND USAGE

The use of regrind is possible, but should be assessed on the basis of the project, moulding parameters, and type of grinding. The effect of using regrind on material properties must be evaluated by the customer on its specific project and process. High percentages of regrind can cause a reduction in viscosity and fibre length, reducing mechanical properties, reducing mechanical properties

### HOT RUNNER MOULDS

Hot runner moulds are not recommended.

## LATER 4 G/30-V0

Compound based on Polybutylene Terephthalate (PBT).  
Glass fibres. UL94 V-0 classified, with halogens, PBB/PBDE free. Product UL certified.

### TO AVOID

Shut-off nozzles and internally heated hot runners have to be avoided. In order to prevent any material degradation, over-dimensioned machines should be avoided.

### CONTACTS

**LATI Industria Termoplastici S.p.A.**

Via F. Baracca, 7 - I - 21040 VEDANO OLONA (VA)

Tel. +39-0332-409111 - Fax +39-0332-409260

[email: techserv@it.lati.com](mailto:techserv@it.lati.com)

<http://www.lati.com>

<http://lambda.lati.it>

### NOTES

**The products mentioned herein are not suitable for applications in contact with foodstuff or for potable water transportation, or for toy manufacturing. The products mentioned herein are not suitable for applications in the pharmaceutical, medical or dental sector.**

Values shown are based on testing of injection moulded laboratory test specimens, conditioned according to the practice and represent data that fall within the standard range of properties for non-coloured material, if not otherwise specified. As they may be subject to variations, these values do not represent a sufficient basis for any part design and are not intended for use in establishing values for specification purposes. Properties of moulded parts can be influenced by a wide range of factors including, but not limited to, colorants, part design, processing conditions, post-treatment conditions, environmental conditions and usage of regrind during the moulding process. If data are explicitly indicated as provisional, range of properties has to be considered wider. This information and technical assistance are provided as a convenience for informational purposes only and are subject to change without notice. The customer shall always ensure that the latest release of technical information is at his own disposal. Lati S.p.A. extends no warranties or guarantee, including a warranty of merchantability of whatever use is made of the product, and make no representations as to the accuracy, suitability, reliability, completeness and sufficiency of the information provided, and assume no responsibility regarding the consequences of its use or for any printing errors. It is the customer's responsibility to inspect and test our products in order to determine to his own satisfaction whether they are suitable for his intended uses and applications or used in conjunction with third-party materials. This application-specific analysis shall at least include preliminary testing to determine the suitability for the customer's particular purpose from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done by us as the manner in which the customer use and the purpose to which utilise our products are beyond our control. Lati S.p.A. does not accept and hereby disclaims liability for, any damages whatsoever in connection with the use of or reliance on this information. No one is authorised to make any warranties, issue any immunities or assume any liabilities on behalf of Lati S.p.A. except in a writing signed by a specifically authorised Lati S.p.A. executive. Unless otherwise agreed in writing, the exclusive remedy for all claims is replacement of the product or refund of the purchase price at Lati's option, and in no event shall Lati S.p.A. be liable for special, consequential, incidental, punitive or exemplary damages. No information herein can be considered as a suggestion to use any product in conflict with intellectual property rights of third-parties. Lati S.p.A. disclaims any liability that may be claimed for infringement or alleged infringement of patents. For any other issues Lati S.p.A. Conditions of Sales apply.  
Copyright © Lati S.p.A. 2008