

Single Pair Flexible Foil Screened cable



Part NO: RGW-1653
Product Code: Single Pair Flexible Foil Screened cable

Product Description

Application:

For communication and signal control systems.

Reference Standard

Customer's sample spec.and the general standard

Multi-construction

2

Cable Construction

Conductor	Tinned Copper
Construction	T0.2±0.003x7
Stranded Dia.(±0.01mm)	0.60
Insulation	PVC
Thickness	0.27
Insulation Dia.(±0.1mm)	1.15
Insulation Color	Red; Black

Drain wire	Tinned Copper
Construction (mm)	T0.2±0.003x7
Al-Pet Shield	coverage >=115%
Jacket	PVC
Thickness(mm)	>=0.65
Dia.(±0.2mm)	3.60
Jacket Color	Black

Marking

Single Pair Flexible Foil Screened cable ww/yy +Meter marking

PACKAGING


100m/Reel

RoHS GUIDELINE			
We operate according to the following standards			
Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls(PBB)	Forbidden	GC/MS	
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	

Revision History

A0-1

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω/Km)	84.6
Min.Insulation DC Resistance at 20°C (MΩ *Km)	>500
Rated Temperature(°C)	-20 to +60
Rated Voltage(V)	30

Label on Reel

Product label

Single Pair Flexible Foil Screened cable

Black

100M

RoHS(2002/95/EC) Compliant

WW/YY

RS label

7492535

100M

Made in China



Date: 2011-09-13

Page: 1 / 1