


Honeywell Sensing and Control




Home > Products > Open Loop > CSL > Product Page

Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Customer Feedback

CSLW6B40M



Actual product appearance may vary.

CSL Series miniature wired open-loop current sensor, 40 mA sensed current, sink or source output, through-hole, operates on ac or dc current, bottom mount

Features

- Wired open-loop design with multiple turns for increased sensitivity
- ac or dc current sensing
- Linear ratiometric output
- Current sinking or sourcing output for interfacing flexibility
- Low insertion loss
- Fast response time
- Compact size for applications with limited space
- Accurate, low-cost sensing
- Minimum energy dissipation
- Maximum current limited only by conductor size
- Built-in temperature compensation promotes reliable operation
- Operating temperature range - 25 ! C to 100 ! C [-13 ! F to 212 ! F]
- RoHs compliant (lead-free)

Potential Applications

- Motor control in applications, HVAC and consumer tools
- Current monitoring of electronic circuits
- Overcurrent protection
- Ground fault detectors
- Robotics
- Industrial process control
- UPS and telecommunication power supplies
- Welding current monitoring
- Battery management systems in mobile equipment
- Watt meters
- Variable speed drives

Description

Honeywell's CSL Series miniature, open-loop current sensors incorporate our SS490 Series miniature ratiometric linear Hall-effect sensor (MRL!). The sensing element is encapsulated in a printed circuit board-mountable plastic package. The combination of sensor, flux collector, housing, and wire coil comprises the current sensor assembly. These sensors are ratiometric.

Supporting Documentation

 [Dimensions](#)


Product Specifications	
Sensor Type	Open Loop Linear
Sensed Current Type	ac or dc
Sensed Current Range	± 40 mA
Package Style	PCB Bottom Mount
Output Type	Sink/Source
Sensitivity	22.4 mV/mA min. to 30.0 mV/mA max.

My Links

- [Login to iCOM](#)
- [Login as Rep/AD](#)
- [Login as Guest](#)
- [Login to Digital University](#)

Keyword Search

Search for product and support information.



Product Search

Part number search:



Use (*) to expand search

→ [Specification Search](#)

Supply Current	9 mA max.
Offset Voltage	Vs/2
Supply Voltage	4.5 Vdc to 10.5 Vdc
Offset Current	1 mA (sinking); 1.5 mA (sourcing)
Offset Shift (%/ °C)	± 0.064
Response Time	3 ! s
Operating Temperature Range	-25 °C to 100 °C [-13 °F to 212 °F]
Storage Temperature Range	-65 °C to 110°C [-85 °F to 230 °F]
Mounting	PCB on 5 pins
Pinout Style	5 pin
Availability	Global
Comment	Rcoil = 120 ohms typ. (Characteristics based on Vs = 5 Vdc, Ta = 25 °C unless specified)
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Series Name	CSL