



Wiha Precision ESD.

The static dissipative precision screwdriver.

ESD screwdriver sets.



272 K6 Precision ESD slotted/ Phillips screwdriver set, 6 pcs.
Dissipative handle, ESD-safe.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Precision handle with rotating cap, surface resistance $10^6 - 10^9$ ohms.

Standards: IEC 61340-5-1.

Application: For working on electrostatically sensitive components.

Extra: Practical plastic rack with hanging holes.
In plastic box, can be opened and positioned on workbench.

Order-No.	Series					
08463 9	272 K6					1
⓪	272	1.5x40	2.0x40	2.5x50	3.0x50	
⊕	273	PH00x40	PH0x50			

ESD screwdriver sets.



277 K6 Precision ESD hex nut driver set, 6 pcs.
Dissipative handle, ESD-safe.

Blade: Chrome-vanadium steel, through hardened, chrome-plated.

Handle: Precision handle with rotating cap, surface resistance $10^6 - 10^9$ ohms.

Standards: IEC 61340-5-1.

Application: For working on electrostatically sensitive components.

Extra: Practical plastic rack with hanging holes.
In plastic box, can be opened and positioned on workbench.

Order-No.	Series					
32279 3	277 K6					1
⓪	277	2.5x60	3x60	3.5x60	4x60	
		5x60	5.5x60			



275 K6 Precision ESD hex screwdriver set, 6 pcs.
Dissipative handle, ESD-safe.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Precision handle with rotating cap, surface resistance $10^6 - 10^9$ ohms.

Standards: IEC 61340-5-1.

Application: For working on electrostatically sensitive components.

Extra: Practical plastic rack with hanging holes.
In plastic box, can be opened and positioned on workbench.

Order-No.	Series					
32278 6	275 K6					1
⓪	275	0.9x40	1.3x40	1.5x50	2x50	
		2.5x60	3x60			



278 K6 Precision ESD TORX® screwdriver set, 6 pcs.
Dissipative handle, ESD-safe.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Precision handle with rotating cap, surface resistance $10^6 - 10^9$ ohms.

Standards: IEC 61340-5-1.

Application: For working on electrostatically sensitive components.

Extra: Practical plastic rack with hanging holes.
In plastic box, can be opened and positioned on workbench.

Order-No.	Series					
26919 7	278 K6					1
⓪	278	T5x40	T6x40	T7x40	T8x40	
		T10x50	T15x60			

Wiha Ceramic.


The non-static adjustment tool for clean rooms.



The Wiha Ceramic precision screwdrivers with blades made of high-tech zirconium ceramic are the perfect tools for all applications in clean rooms and for delicate electrostatic components. In these areas there are high requirements in terms of eddy-current losses.

The ceramic blades and handles are completely antimagnetic and anti-static. This is a fundamental requirement for working with highly

sensitive components, such as capacitors, solenoids and various resistances. The ceramic blades are resistant to mechanical wear, acid corrosion and thermal shock stress. Wiha Ceramic screwdrivers are available with slotted and Phillips tips, as well as in a set.



With centring head and quick-turning zone for optimum handling.



The ceramic blade and handle are completely anti-magnetic and anti-static.



Wiha Ceramic.

- Ideal for adjusting electrical components
- Suitable for working in clean rooms
- Anti-static and anti-magnetic handle and blade
- Rotating cap for easy working
- Resistant to mechanical wear, thermal shock stress and acidic corrosion

For slotted and Phillips screws.



270 Ceramic slotted screwdriver.
Non-static adjustment tool with ceramic blade.

Blade: Made of high-quality special ceramic, anti-static/ anti-magnetic.

Handle: Wiha Proturm® Precision handle with rotating cap, anti-static/ anti-magnetic.

Application: Specially designed for tuning and adjusting high frequency devices, suited to cleanrooms.

Order-No.	⓪	⊕	⓪	⊕	⊕	⊕
02163 4	0.9	15	0.35	1.75	94.5	12.5
02164 1	1.3	15	0.35	1.75	94.5	12.5
02167 2	1.8	15	0.35	1.75	94.5	12.5
02168 9	2.6	15	0.35	2.6	94.5	12.5



271 Ceramic Phillips screwdriver.
Non-static adjustment tool with ceramic blade.

Application: Specially designed for tuning and adjusting high frequency devices, suited to cleanrooms.

Order-No.	⊕	⊕	⓪	⊕	⊕	⊕
02169 6	PH0	15	2.6	94.5	12.5	10

Ceramic screwdriver set.



270 HK3 Ceramic slotted/ Phillips screwdriver set, 3 pcs.
Non-static adjustment tool with ceramic blade.

Blade: Made of high-quality special ceramic, anti-static/ anti-magnetic.

Handle: Wiha Proturm® Precision handle with rotating cap, anti-static/ anti-magnetic.

Application: Specially designed for tuning and adjusting high frequency devices, suited to cleanrooms.

Extra: Delivered in practical plastic box.

Order-No.	Series			
02171 9	270 HK3			1
⓪	270	0.9x15	2.6x15	
⊕	271	PH0x15		