

PARATHOM MR16 35 24° ADV 6.5 W/827 GU5.3

PARATHOM MR16 advanced | Dimmable low-voltage LED reflector lamps MR16 with retrofit pin base



Areas of application

- As a downlight for marking walkways, doors, stairs, etc.
- Exhibitions, department stores
- Outdoor use in outdoor luminaires only (minimum IP65)
- Directional light sources
- Museums
- Hospitality
- Shops

Product benefits

- Very low energy consumption
- Extremely long life
- Robust against vibrations
- No UV and near-IR radiation in the light beam
- Efficient generation of white light

Product features

- Professional LED lamp
- Dimmable (with many common dimmers, see also www.osram.com/dim)
- Base: GU5.3
- Lifetime: up to 25,000 h
- Mercury-free lamps
- High color consistency



Technical data

Electrical data

Rated wattage	5.90 W
Nominal wattage	5.90 W
Nominal voltage	12 V
Claimed equiv. conventional lamp power	35 W
Operating frequency	50...60 Hz
Power factor λ	0.70

Photometrical data


Luminous intensity	1100 cd
Nominal luminous flux	350 lm
Rated luminous flux	350 lm
Color temperature	2700 K
Color rendering index Ra	80
Lumen main.fact.at end of nom.life time	0.70
Light color as per EN 12464-1	Warm White
Standard deviation of color matching	≤ 5 sdcn
Nominal useful luminous flux 90°	350 lm
Rated useful luminous flux 90°	350 lm
Rated peak intensity	1050 cd

Light technical data

Beam angle	24 °
Warm-up time (60 %)	< 0.20 s
Starting time	< 0.5 s
Nominal beam angle	24.00 °
Rated beam angle (half peak value)	24.00 °

Dimensions & weight

Product datasheet



Overall length	51.0 mm
Diameter	34.7 mm
Outer bulb	MR51
Length	51.0 mm
Maximum diameter	50.0 mm

Lifespan

Nominal lamp life time	25000 h
Rated lamp life time	25000 h
Number of switching cycles	100000

Additional product data

Base (standard designation)	GU5.3
Mercury-free	Yes
New article	NEW
Appropriate disposal acc. to WEEE	Yes
Footnote only for product	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value/LED lamps contain several electronic components. Under unfavourable conditions these can lead to acoustic noise. In case of resonance even low noise can cause audible effect. Possible factors influencing this are the installation, the design of the lamp holder and the luminaire (acoustic resonance effect) as well as the dimmer or the transformer (harmonics or electronic resonance)

Capabilities

Dimmable	Yes ¹⁾
-----------------	-------------------

¹⁾ With many common dimmers

Product datasheet


Certificates & standards

Energy efficiency class	A
Energy consumption	7 kWh/1000h

Country specific categorizations

ILCOS	DRPAR-6,5/827-12-GU5.3-50/36
Order reference	PMR163524AD 6,5

Light Distribution



Spectral power distribution



Guarantee

Product datasheet

Equipment / Accessories

- Equipped with high-power LEDs
 - Suitable for many commercially available electronic or conventional transformers
-

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321884992	PARATHOM MR16 35 24° ADV 6.5 W/827 GU5.3	Shipping carton box 10	71 mm x 114 mm x 271 mm	2.19 dm ³	637.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

For dimming conformity see

- ▶ www.osram.com/DIM

For further products and actual information concerning LED lamps see

- ▶ www.osram.com/ledlamps

— For Guarantee see

- ▶ www.osram.com/guarantee

Further information see

- ▶ www.osram.com/low-voltage-ledlamps
-

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.