



### Main

Range of product	NG160
Device short name	NG160N
Circuit breaker name	NG160N
Circuit breaker application	Distribution
Poles description	3P
Protected poles description	3t
Network type	AC
Network frequency	50/60 Hz
[In] rated current	125 A ( 40 °C )
Breaking capacity code	N
Breaking capacity	40 kA Icu conforming to IEC 60947-2 at 220...240 V AC 50/60 Hz 25 kA Icu conforming to IEC 60947-2 at 380...415 V AC 50/60 Hz 16 kA Icu conforming to IEC 60947-2 at 440 V AC 50/60 Hz 10 kA Icu conforming to IEC 60947-2 at 500 V AC 50/60 Hz
[Ics] rated service breaking capacity	Ics 18.75 kA 380/415 V AC 50/60 Hz Ics 12 kA 440 V AC 50/60 Hz Ics 7.5 kA 500 V AC 50/60 Hz Ics 30 kA 220/240 V AC 50/60 Hz
Suitability for isolation	Yes
Trip unit technology	Thermal-magnetic
Trip unit rating	125 A

### Complementary

Control type	Toggle
Mounting mode	Clipped
Mounting support	35 mm symmetrical DIN rail
Upside connection	Front
Downside connection	Front
Connections - terminals	Tunnel type terminals
Mechanical durability	10000 cycles
Electrical durability	5000 cycles 440 V
Local signalling	ON/OFF indication
Magnetic tripping current	1250 A
Long time pick-up adjustment type Ir	Fixed
Earth-leakage protection	Separate block
Height	120 mm
Width	90 mm
Depth	82.5 mm
Product compatibility	Single terminal

### Environment

Standards	IEC 60947-3
-----------	-------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Contractual warranty

---

Period	18 months
--------	-----------

---