

Single phase, non-stabilised dc power supply **GLC 230/24-3**



Advantages

- Fuse protection in the input and a fuse protection for the output
- Separate windings
- Capacitor accessories
- Double screw terminals on the output
- DC OK signalling via LEDs
- Panel installation on mounting rails

Applications

Robust direct current power is concentrated on the core task of voltage and power supply.

Standards



Non-stabilised dc power supply / Safety isolating transformer
to VDE 0570 part 2-6, EN 61558-2-6, IEC 61558-2-6, UL 1012

Approvals




UL 5085-1/-2, CSA 22.2 No.66



Single phase, non-stabilised dc power supply GLC 230/24-3

Type		GLC 230/24-3
Electrical data	Input	
	Input rated voltage	230 Vac
	Rated frequency	50 - 60 Hz
	Output	
	Output rated voltage	24 Vdc
	Power	72.00 W
	Output rated current	3.00 A
	Ripple factor	#5 %
	Standards	
	Classification	Single phase non-stabilised dc power supply / safety isolating transformer
	Approvals	
	Approvals	cURus (transformer only)
	Environment	
	Cooling method	by self cooling
	Ambient temperature max.	60° C
Safety and protection		
Type	enclosed	
Class of Insulation System	E	
Protection index	IP 00	
Safety class (prepared)	II	
Short circuit strength	short-circuit proof	
Order numbers		
Order Number	GLC 230/24-3	

Type		GLC 230/24-3
Mechanical data	Terminal and mounting	
	Terminals	Screw-type terminals
	Fixing method	DIN Rail system TH 35
	Measures and weights	
	Weight	2.30 kg



Subjects to change.