


ZEICHNUNG GESCHÜTZT DURCH
©COPYRIGHT 1988
AMP DEUTSCHLAND GMBH
ALLE RECHTE VORBEHALTEN

REV.	ÄNDERUNG	DATUM	NAME
2	ZEICHNUNG IN EUROPEAN PROJECTION GEÄNDERT	29.11.90	A.HO
3	LÖTLÄNGE VON 3.0 IN 3.1 GEÄNDERT	12.03.92	A.HO
C	VERPACKUNGSANGABE HINZU	15.01.96	F.RDT
C1	NOTE 3 CHANGED FROM SnPb INTO Sn	23.03.06	K.-H. HESS

DO NOT SCALE
DIMENSIONS IN mm





METRIC

EUROPEAN
PROJECTION



NOTES:

- TO DETERMINE DIMENSIONS TAKE $N = \text{NR. OF POS.}$.
FOR EXAMPLE: 10 POS.: $N \times 2,54 = 25,4 \text{ mm.}$
FOR ORDERNR. USE BASIC NR. + NR. OF POS.
FOR EXAMPLE: 2 POS. = 215 299-2 (SHORTEST VERSION)
36 POS. = 3-215 299-6 (LONGEST VERSION)
- HOUSING MATERIAL: GREEN GLASSFILLED POLYESTER,
UL 94V-0
CONTACT MATERIAL: PHOSPHORBRONZE.
- PLATING: UNDERCOATING: $1,3 \mu\text{m Ni.}$
AT CONT. PLACE: $0,8 \mu\text{m Au.}$
AT SOLDER-TYNES: MIN. $2,5 \mu\text{m Sn}$
- MATES WITH 0,63 SQUARE/ROUND MODU POSTS.
- CONTACT-POINT.
- RECOMMENDED P.C. BOARD-THICKNESS: 1,6.
- RETENTION FEATURE.
- HV100 CONNECTOR PACKED IN ANTISTATIC BLISTER



P.C.-BOARD HOLE-PATTERN

NICHT TOLERIERTE MASSE
± 0,1
± -
MASSTAB 5:1

VERWENDET FÜR E 92-9803	SEE NOTES	SEE NOTES	SEE NOTES
	FINISH	MATERIAL	PARTNUMBER
CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED	AMP AMP-HOLLAND B.V. 's-Hertogenbosch, The Netherlands.		
	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 14.8.1986		
	© COPYRIGHT 1986 BY AMP-HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.		
	DR. L.V.D.HEYDEN	DATE 09.07.86	REV. DATE D M Y 150196
CHK. W.SIMONS	DATE	WIRE RANGE -	NAME HV 100 VERTICAL CONNECTOR
APP. L.V.SOEST	DATE	INSUL. RANGE -	SINGLE ROW, 8,5mm HEIGHT, TOP ENTRY, GOLD, MAX. 36 POSITIONS.
SIZE A3		SHEET 1 OF 1	DWG. No. 215299
			REV. LTR. C1

8 7 6 5 4 3 2 1