



PRODUCT SPECIFICATION

PRODUCT SPECIFICATION OF THE 0.30MM CENTER FFC JUMPER CABLE

Revision List

REVISION	MODIFICATION	SHEETS	DATE
A	First Release	1 - 5	2011/11/15

REVISION: A	ECR/ECN INFORMATION: EC No: USW2012-0123 DATE: 2011/11/01	TITLE: PRODUCT SPECIFICATION 0.30MM CENTER FFC JUMPER CABLE	SHEET No. 1 of 5
DOCUMENT NUMBER: PS-15015-001	CREATED / REVISED BY: M. Imig	CHECKED BY: J. Wolfsberger	APPROVED BY: S. Fulton



PRODUCT SPECIFICATION

1 SCOPE

This specification covers the 0.30mm center FFC (Flat Flexible Cable) jumper cable, high temperature style, using gold plated copper conductor.

2 PRODUCT DESCRIPTION

2.1 Product name and series number

Product name: 0.30MM CENTER FFC JUMPER CABLE

Product material no: 15015-XXXX

2.2 Dimensions, materials and markings

Product dimensions according SD-15015-001.

Number of conductors N: 23, 25, 27, 29, 33, 39, 45, & 51

Pitch P: $0.30 \pm 0.05\text{mm}$

Span E: $0.30 (N-1) \pm 0.10\text{mm}$

Total width W: $0.30 (N+1) \pm 0.10\text{mm}$

Margin width M: $0.30 + 0.15\text{mm} / -0.096\text{mm}$


Exposed Contacts S: $3.00\text{mm} \pm .50\text{mm}$

End thickness Tc: $0.80 \pm 0.05\text{mm}$

Thickness - insulated area Ti: $0.12 \pm 0.05\text{mm}$

Length L: 2.00", 4.00", 6.00", 8.00", & 10.00" $\pm .01$ "

Reinforcement length F: $4.00 \pm .50\text{mm}$



REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
A	EC No: USW2012-0123 DATE: 2011/11/01	PRODUCT SPECIFICATION 0.30MM CENTER FFC JUMPER CABLE	2 of 5
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-15015-001	M. Imig	J. Wolfsberger	S. Fulton



PRODUCT SPECIFICATION

2.3 COMPOSITION

- Conductor: Material: Gold plated copper conductor
Thickness: 0.018mm nominal
- Insulation tape: Material: Polyimide + Flame retardant adhesive
Thickness: 0.025mm nominal
Color: Orange - Brown
- Reinforcement tape: Material: Polyimide + Adhesive
Thickness: 0.135mm nominal
Color: Orange – Brown

2.4 Safety agency approvals

Not applicable.

3 RATINGS

3.1 Current and applicable conductors

Cross section	Amps
0.0018mm ²	0.2

3.2 Temperature

Operating temperature: -40°C to +105°C

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
A	EC No: USW2012-0123 DATE: 2011/11/01	PRODUCT SPECIFICATION 0.30MM CENTER FFC JUMPER CABLE	3 of 5
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-15015-001	M. Imig	J. Wolfsberger	S. Fulton



PRODUCT SPECIFICATION

4 PERFORMANCE

4.1 Electrical requirements

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENT
1	Conductor resistance	20mV Maximum, 10mA Maximum	60 milliohm Maximum
2	Insulation resistance cond. to cond.	250 V DC between adjacent terminal and ground	50 Mohms Minimum
3	Dielectric test	Mate with molex series 502598 and apply 200 V AC for 1 minute between adjacent terminal or ground	No disruptive discharge
4	Voltage rating	Maximum 30°C heat rise at mate with Molex series 502598	50 V AC(rms)/DC MAXIMUM
5	Current rating		0.2 A MAX

4.2 Physical requirements

ITEM	DESCRIPTION	TEST CONDITION	REQUIREMENT
6	Temperature rating		-40°C to +105°C
7	Heat resistance	Mate Molex series 502598 and expose to 85°C for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions 1 to 2 hours, after which the specified measurements shall be performed.	1) No Damage 2) contact resistance of 100 milliohm Maximum
8	Thermal shock	Mated Molex series 502598 and subject to the following conditions for 5 cycles. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room condition for 1 to 2 hours, after which the specified measurements shall be performed. 1 cycle 30 minutes at -55°C 5 minutes at +25°C 30 minutes at +85°C 5 minutes at +25°C	1) No Damage 2) contact resistance of 100 milliohm Maximum

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
A	EC No: USW2012-0123 DATE: 2011/11/01	PRODUCT SPECIFICATION 0.30MM CENTER FFC JUMPER CABLE	4 of 5
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-15015-001	M. Imig	J. Wolfsberger	S. Fulton



PRODUCT SPECIFICATION

9	Cold coiling	96 hours at -40°C / The sample will be wound on a 3mm dia. Mandrel	1) Insulation resistance (item 2 above) 2) Dielectric test (item 3 above) 3) Visual inspection
10	Wear by abrasion	Test following EN3475-503 Weight: 500g Speed: 60 cycles/min Abrasion tool: 0.13mm dia.	10000 cycles (standard) 1000 cycles (shielded) MINIMUM
11	Folding	The specimen shall be folded manually (Bending angle: 180° / Radius: 4mm)	20 times MINIMUM
12	Moisture resistance	Mate with Molex series 502598 and expose to 40°C, relative humidity 90 to 95% for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 hour, after which the specified measurements shall be performed.	1) No Damage 2) contact resistance of 100 milliohm Maximum 3) meet dielectric requirement (item 3 above) 4) insulation resistance be 20 Mohm Minimum

5 PACKAGING

According to MOLEX packaging specification: PK-15015-001

6 ROHS COMPLIANCE

Cable construction is RoHS compliant. This includes base FFC.

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
A	EC No: USW2012-0123 DATE: 2011/11/01	PRODUCT SPECIFICATION 0.30MM CENTER FFC JUMPER CABLE	5 of 5
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-15015-001	M. Imig	J. Wolfsberger	S. Fulton