





NO	DESCRIPTION	DATE
①	BACKGROUND FORMAT UPDATED	06.25.02'
②	BACKGROUND FORMAT UPDATED GOLD 3μ " MIN. $\longrightarrow$ GOLD	04.07.09'
③	DEL. PROOF VOLTAGE WORKING VOLTAGE $\longrightarrow$ VOLTAGE RATING ADD 3.2 MAX. PANEL	04.24.13'



MOUNTING HOLE

1.0 ELECTRICAL

1.1 FREQUENCY RANGE: DC-18 GHz

1.2 NOMINAL IMPEDANCE: 50 OHMS

1.3 VOLTAGE RATING: 500 VOLTS MAX. ③

1.4 VSWR: 1.23 MAX.

2.0 MATERIALS

2.1 BODIES: BRASS PER JIS-C3604

2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300

2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A

5.0 ENVIRONMENTAL

5.1 OPERATING TEMPERATURE RANGE: -65° C TO +165° C

5	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD 50μ " MIN.
4	INSULATION	TEFLON	1	NONE
3	BODY	BRASS	1	GOLD 3μ " MIN.
2	WASHER	BRASS	1	GOLD
1	NUT	BRASS	1	GOLD
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



APPROVED

by _____ DATE: _____

DESCRIPTION		SMA STRAIGHT BULKHEAD JACK RECEPTACLE									
製圖	DRAWN	TOLERANCE		品名	19-16-3	T.G.G	日期	DATE	版次	REV.	
	Yoko	.X	±0.2	TITLE	\ROHS COMPLIANT <50Ω>			11.22.95'		A-3	
檢圖	CHECK	.XX	±0.1	單位	mm(in)	DWG.NO. 19-0148					
	Arc	.XXX	±0.05	比例	SCALE						
認定	APPROVAL	ANGLE	±5°								
	Jenny										