




SECTION C - C



RECOMMENDED P.C.BOARD LAYOUT



NOTES:

1. MOLDED RIBS TO PROVIDE AN INTERFERENCE FIT TO A 1.62± 0.10/(.064±.004) P.C. BOARD
2. PLATING
POSTPLATE 0.00254/(.000100) MIN. TIN OVER 0.00127/(.000050) MIN. NICKEL OVERALL.
3. PART INTENDED TO MATE WITH HOUSING 8981-4P2 AND TERMINAL 8980-3*.
4. PRODUCT SPEC. PS-8981-4SM* APPLIES.
5. MATERIAL:
HOUSING - PET, GLASS FILLED, UL94V-0, COLOR: BLACK
TERMINAL - PHOSPHOR BRONZE

OBS TIN/LEAD P/N EC NO: S2006-0763 DRWN:MLONG 2006/03/31 CHKD:NAGESHKN 2006/03/31 APPR:PTLIM 2006/04/03	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY CK	DATE 1989/09/30	TITLE POWER CONNECTOR, 4 CKTS SMT		
			4 PLACES	± ---	± ---	CHECKED BY TAY	DATE 1989/09/30			
			3 PLACES	± ---	± .008	APPROVED BY NK	DATE 1989/09/30			
			2 PLACES	± 0.20	± ---	MATERIAL NO. SEE TABLE		DOCUMENT NO. SDA-8981-4SM1		SHEET NO. 1 OF 1
			1 PLACE	± ---	± ---					
			ANGULAR ± 3 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	