

1

2 3

4

5

6

PRODUCT NUMBER

71918-YXX


TOTAL NB OF POSITIONS 06 TO 64

LATCHING

0= WITHOUT LATCH




1= STANDARD LATCH

2= LOW PROFILE LATCH



NOTES:

- 1 - HOUSING MAT'L : GLASS FILLED THERMOPLASTIC. UL94V-0 COLOR: GREY
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PRODUCT PACKAGED IN TUBES
- 4 - 40N MIN LATCH RETENTION FORCE AT FIRST EXTRACTION
- 5 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- 6 - NO CENTRAL SLOT ON POSITIONS 6 & 8
- 7 - NO LEFT POLARIZATION ON POSITIONS 06, 08, 10, 14.
- 8 - 4.5mm SOLDER TAIL
ORDER 71918-4XX (WITH STANDARD LATCH ONLY)



mat'l. code SEE NOTES				tolerances unless otherwise specified		CUSTOMER COPY	 ELECTRONICS www.fciconnect.com	title	product family	code
ltr	ecn	no	dr	date						
R	F04-0198	LMU	04.05.28	linear	.X ±0.3	projection		SHR.EL.HEADER	QUICKIE	213
					.XX ±0.15			STR DR TMT		
					.XXX ±0.05	mm				
K	F10149	LMU	01.02.22	angles		scale				
L	F10309	DLE	01.05.10	dr	D.LE	01.01.24				
M	F03-0257	LMU	03.08.31	engr	JM.C	01.01.24				
N	F04-0121	LMU	04.01.27	chr	JF.N	01.01.24				
P	F04-0176	LMU	04.04.22	appd	JM.C	01.01.24				
sheet	revision	R	M							
index	sheet	1	2							

1

2

3

4

5

6

Tous droits strictement réservés. Reproduction ou communication
sans autorisation écrite de FCI Electronics S.A.
Propriété de FCI Electronics S.A.
Droits de reproduction FCI Electronics S.A.



All rights strictly reserved. Reproduction or use in third parties
in any form is not permitted without written authority from the
Property of FCI Electronics S.A.
Copyright FCI Electronics S.A.




CORE RANGE

LATCHING	Nbr OF POSITIONS
1	06
1	08
1	10
1	14
1	16
1	18
1	20
1	26
1	30
1	34
1	40
1	44
1	50
1	60
1	64

LATCHING
0 = WITHOUT LACHING
1 = STANDARD LATCH
2 = LOW PROFILE LATCH

PLATING
0.76µm GOLD ON CONTACT AREA
3.81µm TIN/LEAD ON TAIL




1 = STANDARD LATCH

CATALOGUE RANGE

LATCHING	Nbr OF POSITIONS
0/2	06
0/2	08
0/2	10
0/2	14
0/2	16
0/2	18
0/2	20
0/2	26
0/2	30
0/2	34
0/2	40
0/2	44
0/2	50
0/2	60
0/2	64

LATCHING
0 = WITHOUT LACHING
1 = STANDARD LATCH
2 = LOW PROFILE LATCH

PLATING
0.76µm GOLD ON CONTACT AREA
3.81µm TIN/LEAD ON TAIL



2 = LOW PROFILE LATCH

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 ELECTRONICS www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ±0.3		projection 	title	SHR.EL.HEADER STR DR TMT	
H	F70143	PNZ	97.02.25		.XX ±0.15					
J	F10120	DLE	01.01.24		.XXX ±0.05					
K	F10149	LMU	01.02.22	angles				product family QUICKIE	code	
L	F10309	DLE	01.05.10	dr	D.LE	01.01.24			213	
M	F04-0176	LMU	04.04.22	engr	JM.C	01.01.24			sheet	
				chr	JF.N	01.01.24		2 of -		
				appd	JM.C	01.01.24				
sheet index		revision sheet								