


SPECIFICATIONS	
CONTACT CARRIER MATERIAL/COLOR	TPU/YELLOW
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/FINISH	STAINLESS STEEL/PASSIVATED
RATED CURRENT [A]	9.0 A
RATED VOLTAGE [V]	600 V
OUTER JACKET MATERIAL/COLOR	PVC/YELLOW
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	5x18 AWG
TEMPERATURE RANGE	-30°C to +90°C (-22°F to +194°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6,13 AND IEC IP67
CABLE RATINGS	UL TYPE 600 V MC 90°C DRY or 75°C WET or SUN RES or CSA FAS90 FT4



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

- "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- CABLE ARMOR IS CONNECTED TO THE COUPLING NUT.

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	<div style="text-align: center;"> <p>TURCK IAC High Technology Sensors and Automation Controls</p> </div> 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	DRFT RDS DATE 03/19/03 DSGN SCALE 1=2.0 DESCRIPTION <div style="text-align: center; font-size: 1.2em;">RSV RKV 58A-*M</div>
MATERIAL <div style="text-align: center;">SEE SPECIFICATIONS</div>	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	UNIT OF MEASUREMENT <div style="text-align: center; font-weight: bold; font-size: 1.1em;">MILLIMETER [INCH]</div>	IDENTIFICATION NO. <div style="text-align: center; font-size: 1.2em;">F</div>	REV <div style="text-align: center; font-size: 1.2em;">F</div>
FINISH <div style="text-align: center;">SEE SPECIFICATIONS</div>	CONTACT TURCK FOR MORE INFORMATION	DO NOT SCALE THIS DRAWING	FILE: 777001822	SHEET 1 OF 1

F	ADD CABLE ARMOR NOTE	CK	09/14/11	36423
REV	DESCRIPTION	BY	DATE	ECO NO.