








NO	DESCRIPTION	DATE
△	BACKGROUND FORMAT UPDATED	11.21.08'



MOUNTING HOLE



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-2 GHz
- 1.2 NOMINAL IMPEDANCE: 75 OHMS
- 1.3 WORKING VOLTAGE: 400 VOLTS MAX.
- 1.4 PROOF VOLTAGE: 1000 VOLTS
- 1.5 VSWR: 1.1 MAX @ 750 MHz
- 1.6 MAX @ 1 GHz

2.0 MATERIALS

- 2.1 BODY: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: PHOSPHOR BRONZE JIS-B5290
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -40° C TO +85° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
8	INSULATION II	TEFLON	1	NONE
7	BODY II	BRASS	1	NICKEL 100μ" MIN.
6	BODY I	BRASS	1	NICKEL 100μ" MIN.
5	CENTER CONTACT	PHOSPHOR BRONZE	1	GOLD
4	INSULATION I	TEFLON	1	NONE
3	WASHER	BRASS	1	NICKEL 100μ" MIN.
2	WASHER	STEEL	1	NICKEL
1	NUT	BRASS	1	NICKEL



APPROVED

by _____ DATE: _____

DESCRIPTION		MINI BNC RIGHT ANGLE PCB MOUNT JACK									
圖 檢 定	DRAWN	Yoko	TOLERANCE	.X	±0.2	品名	56-07	T.G.N	日期	DATE	版次
	CHECK	Monica	.XX	±0.1		TITLE	ROHS COMPLIANT (750)			04.13.07'	A-1
	APPROVAL	Monica	.XXX	±0.05		單位	mm(In)	DWG.NO.	56-0006		
	SCALE	4:1	ANGLE	±5°		比例					