

3M™ 725 Workstation Monitor Properties

	Typical Properties
Dimensions	2.5 in. x 2.6 in. x 1.1 in. (6.4 cm x 6.6 cm x 2.8 cm)
Power Supply	9 Volt alkaline battery (not supplied)
Test Voltage	9 Vdc maximum
Test Current	Less than 1 microamp
Upper Resistance Limits	Wrist Strap: 35 Megohms Ground Clip: 10 Megohms
Accuracy	± 15%
Environmental Operating Conditions Temperature:	Max. 110° F (43° C) Min. 50° F (10° C)
Humidity:	Max. 75% R.H.
Accessories	723 Belt Clip