






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00						
			W4	REVISED PER ECO-11-008710	27APR11	HMR	JG



RECOMMENDED HOLE LAYOUT

- 1 .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 .000100 BRIGHT TIN OVER .000050 NICKEL.
- 6 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 7 .000100 MATTE TIN OVER .000050 NICKEL.
- 8 HIGH TEMPERATURE CONFIGURATION
- 9 STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- 10 SUPERSEDED BY P/N 5-103639-2.
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHUEY	05MAR91	 TE Connectivity				
		CHK L.CASTAGNA	27MAR93					
DIMENSIONS: mm [INCHES]		APVD L.CASTAGNA	27MAR93	NAME				
		PRODUCT SPEC 108-25034		HDR ASSY, VERT, SINGLE ROW 2.54 [100] C/L 0.64 [025] SQ POST, WITH PLZN & LATCHING, AMPMODU MTE				
		APPLICATION SPEC 114-25026						
		MATERIAL		WEIGHT —		SIZE A2	CAGE CODE —	DRAWING NO C=103639
HOUSING: SEE TABLE		CUSTOMER DRAWING		SCALE 4:1		SHEET 1 of 2		REV W4

