

Antenna - RAD-ISM-2400-ANT-PAN- 8-0 - 2867610

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Panel antenna, degree of protection IP55, 8 dBi gain, linear vertical, SMA (female), impedance 50 ohms, apex angle h/v 75°/70°



Why buy this product

- For large distances with a line of sight

Key commercial data

Packing unit	1 pc
GTIN	 4 017918 938994
Weight per Piece (excluding packing)	147.6 g
Custom tariff number	85177019
Country of origin	Poland

Technical data

Dimensions

Width	80 mm
Height	100 mm
Length	20 mm

Ambient conditions

Degree of protection	IP55
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C

General

Frequency range	2.4 GHz 2.3 GHz ... 2.8 GHz
Horizontal beamwidth	75 °
Vertical beamwidth	70 °
Impedance	50 Ω
Gain	8 dBi
Wind velocity	160 km/h (Has a force of 15 N)

Antenna - RAD-ISM-2400-ANT-PAN- 8-0 - 2867610

Technical data

General

Connection method	SMA (female)
-------------------	--------------

Classifications

eCl@ss

eCl@ss 4.0	27250312
eCl@ss 4.1	27250312
eCl@ss 5.0	19070102
eCl@ss 5.1	19070102
eCl@ss 6.0	19070102
eCl@ss 7.0	19070102
eCl@ss 8.0	19070102

ETIM

ETIM 2.0	EC000416
ETIM 3.0	EC001698
ETIM 4.0	EC001698
ETIM 5.0	EC001698

UNSPSC

UNSPSC 6.01	43171611
UNSPSC 7.0901	43221706
UNSPSC 11	43171611
UNSPSC 12.01	43221706
UNSPSC 13.2	43221706