

## Araldite® Wood Repair

### Two part polyester synthetic wood

#### Other commercial names

- Arabois

#### Key properties

- Fills holes and cracks
- Machinable like wood
- Paintable

#### Description

Araldite Wood Repair is a two part polyester resin which can be used as a synthetic wood to make repair works. After curing, Araldite Wood Repair can be drilled, machined and painted just like wood and is resistant to extreme temperatures from -20°C until 150°C and to external conditions.

#### Product data

Property	Araldite Wood Repair Resin	Araldite Wood Repair Powder
Colour (visual)	Yellow	Brown
Specific gravity	1.1 g.cm <sup>-3</sup>	0.85 g.cm <sup>-3</sup>
Viscosity at 25°C (Pa.s)	0.7 – 0.95	Powder
Pot Life – Liquid application	10 minutes	
Pot Life – Mastic application	4 minutes	

#### Processing

##### Pretreatment

The success of repair works is dependant on proper treatment of the substrates used.


At the very least, joint surfaces should be cleaned with a good degreasing agent in order to remove all traces of oil, grease and dirt.

Alcohol, gasoline (petrol) or paint thinners should never be used.

It is recommended to abrade the surface with sandpaper before applying Araldite Wood Repair.

Mix ratio	Liquid application	Mastic application
Araldite Wood Repair / Resin	4 volumes	2 volumes
Araldite Wood Repair / Powder	3 volumes	3 volumes

The resin and the powder should be blended until they form a homogeneous mix.



## Application of the product

For a liquid application, the product can be applied with a spatula, with a paintbrush or with a spraying gun. For a mastic application, the product can be applied with a spatula or with a knife. If a high thickness is needed, the product can be applied in several layers, in this case at least 15 minutes curing should be allowed between 2 layers.

## Equipment maintenance

All tools can be cleaned with a good degreasing agent like acetone, operatives should take the appropriate precautions and, in addition, avoid skin and eye contact.

## Minimum curing time

Temperature	20°C
Liquid application	14 minutes
Mastic application	6 minutes

---

## Storage

Araldite® Wood Repair may be stored for up to 1 year in the original packaging at room temperature.

---

## Handling precautions

### Caution

Our products are generally quite harmless to handle provided that certain precautions normally taken when handling chemicals are observed. The uncured materials must not, for instance, be allowed to come into contact with foodstuffs or food utensils, and measures should be taken to prevent the uncured materials from coming in contact with the skin, since people with particularly sensitive skin may be affected. The wearing of impervious rubber or plastic gloves will normally be necessary; likewise the use of eye protection. The skin should be thoroughly cleansed at the end of each working period by washing with soap and warm water. The use of solvents is to be avoided. Disposable paper - not cloth towels - should be used to dry the skin. Adequate ventilation of the working area is recommended. These precautions are described in greater detail in the Material Safety Data sheets for the individual products and should be referred to for fuller information.

Huntsman Advanced Materials  
(Switzerland) GmbH  
Klybeckstrasse 200  
4057 Basel  
Switzerland

Tel: +41 (0)61 299 11 11

www.go-araldite.com  
Emergency number : + 32 35 751 234

Huntsman Advanced Materials warrants only that its products meet the specifications agreed with the buyer. Typical properties, where stated, are to be considered as representative of current production and should not be treated as specifications.

The manufacture of materials is the subject of granted patents and patent applications; freedom to operate patented processes is not implied by this publication.

While all the information and recommendations in this publication are, to the best of our knowledge, information and belief, accurate at the date of publication, NOTHING HEREIN IS TO BE CONSTRUED AS A WARRANTY, EXPRESS OR OTHERWISE. IN ALL CASES, IT IS THE RESPONSIBILITY OF THE USER TO DETERMINE THE APPLICABILITY OF SUCH INFORMATION AND RECOMMENDATIONS AND THE SUITABILITY OF ANY PRODUCT FOR ITS OWN PARTICULAR PURPOSE.

The behaviour of the products referred to in this publication in manufacturing processes and their suitability in any given end-use environment are dependent upon various conditions such as chemical compatibility, temperature, and other variables, which are not known to Huntsman Advanced Materials. It is the responsibility of the user to evaluate the manufacturing circumstances and the final product under actual end-use requirements and to adequately advise and warn purchasers and users thereof.

Products may be toxic and require special precautions in handling. The user should obtain Safety Data Sheets from Huntsman Advanced Materials containing detailed information on toxicity, together with proper shipping, handling and storage procedures, and should comply with all applicable safety and environmental standards.

Hazards, toxicity and behaviour of the products may differ when used with other materials and are dependent on manufacturing circumstances or other processes. Such hazards, toxicity and behaviour should be determined by the user and made known to handlers, processors and end users.

Except where explicitly agreed otherwise, the sale of products referred to in this publication is subject to the general terms and conditions of sale of Huntsman Advanced Materials LLC or of its affiliated companies including without limitation, Huntsman Advanced Materials (Europe) BVBA, Huntsman Advanced Materials Americas Inc., and Huntsman Advanced Materials (Hong Kong) Ltd.

Huntsman Advanced Materials is an international business unit of Huntsman Corporation. Huntsman Advanced Materials trades through Huntsman affiliated companies in different countries including but not limited to Huntsman Advanced Materials LLC in the USA and Huntsman Advanced Materials (Europe) BVBA in Europe.

Araldite® is a registered trademark of Huntsman Corporation or an affiliate thereof.

Copyright © 2011 Huntsman Corporation or an affiliate thereof. All rights reserved.