



ENGLISH

Datasheet

Stock No: 811-4384

RS Pro BASEC 4 Core White Unscreened 3184Y Solid PVC Power Cable H05VV-F, 0.75 mm² CSA 6 A, 300 V, 500 V



Image representative of range

Product Details

BASEC approved H05VVF/3184Y 4 Core Cable

A light duty cable used for domestic appliances, kitchens and offices. They are also designed for use with light portable appliances such as radios, table lamps and office equipment.

Features and Benefits

- PVC Insulation
- Flexible copper conductor - EN 60228 Class 5

Note

Cable is not suitable for outdoor use or uindustrial applications

Standards

BASEC, EN 50525-2-11, EN/IEC 60332-1-2

Flexible PVC Cable

Specifications:

Number of Cores	4
Cross Sectional Area	0.75 mm ²
Sheath Colour	White
Current Rating	6 A
Voltage Rating	300 V, 500 V
Outer Diameter	8.3mm
Sheath Material	Polyvinyl Chloride PVC
Harmonised Code	H05VV-F
Type	3184Y
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+70°C
Screened/Unscreened	Unscreened
Conductor Strand Type	Solid
Number of Strands	24
Core Strands	24/0.2 mm
American Wire Gauge	18 AWG
Size of Strands	0.2 mm
Conductor Resistance	26 Ω/km
Insulation Material	PVC Type TI1 to BS7655
Standards Met	BASEC
Conductor Material	Copper