

Industrial Ethernet Switch - FL SWITCH SFN 5TX-24VAC - 2891021

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Ethernet switch, 5 TP RJ45 ports, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function

Your advantages

- ✓ Auto negotiation and autocrossing detection simplifies installation and setup
- ✓ Local diagnostic indicators with LEDs
- ✓ The switch also offers cable locking and port blocking
- ✓ QoS-prioritized (Quality of Service) messages
- ✓ RJ45 ports support a transmission speed of 10/100 Mbps; fiber optic ports support 100 Mbps
- ✓ DC and AC power supplies



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 457156 |
| GTIN | 4046356457156 |
| Weight per Piece (excluding packing) | 277.000 g |
| Custom tariff number | 85176200 |
| Country of origin | Taiwan |

Technical data

Note

| | |
|-------------------------|---|
| Utilization restriction | EMC: class A product, see manufacturer's declaration in the download area |
|-------------------------|---|

Dimensions

| | |
|--------|--------|
| Width | 30 mm |
| Height | 120 mm |
| Depth | 70 mm |

Ambient conditions

Industrial Ethernet Switch - FL SWITCH SFN 5TX-24VAC - 2891021

Technical data

Ambient conditions

| | |
|--|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | 0 °C ... 60 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Air pressure (operation) | 86 kPa ... 108 kPa (up to 1500 m above sea level) |
| Air pressure (storage/transport) | 66 kPa ... 108 kPa (up to 3500 m above sea level) |

Interfaces

| | |
|-------------------------------|-----------------------------------|
| Interface | Ethernet (RJ45) |
| No. of ports | 5 (RJ45 ports) |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission speed | 10/100 Mbps |

Function

| | |
|----------------------------------|---|
| Basic functions | Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode |
| Additional functions | Autonegotiation |
| Status and diagnostic indicators | LEDs: U _S , link and activity per port |

Network expansion parameters

| | |
|---|--|
| Cascading depth | Network, linear, and star structure: any |
| Maximum conductor length (twisted pair) | 100 m |

Supply voltage

| | |
|-----------------------------|--|
| Supply voltage | 24 V AC/DC |
| Residual ripple | 3.6 V _{PP} (within the permitted voltage range) |
| Supply voltage range | 20 V AC ... 28 V AC |
| | 12 V DC ... 32 V DC |
| Typical current consumption | 114 mA (at U _S = 24 V AC) |

General

| | |
|------------------|--------------|
| Mounting type | DIN rail |
| Type AX | Block design |
| Net weight | 277 g |
| Housing material | Aluminum |

Standards and Regulations

| | |
|---|--|
| Electromagnetic compatibility | Conformance with EMC Directive 2004/108/EC |
| Noise emission | EN 61000-6-4 |
| Noise immunity | EN 61000-6-2:2005 |
| Vibration (storage/transport) | 5g, 150 Hz, in acc. with IEC 60068-2-6 |
| Free from substances that could impair the application of coating | In acc. with VW specification |

Industrial Ethernet Switch - FL SWITCH SFN 5TX-24VAC - 2891021

Technical data

Standards and Regulations

| | |
|-----------------------|--|
| Vibration (operation) | in acc. with IEC 60068-2-6: 5g, 150 Hz |
| UL, USA/Canada | Class I, Div. 2, Groups A, B, C, D |

Environmental Product Compliance

| | |
|------------|---|
| | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 10; |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 19170402 |
| eCl@ss 4.0 | 27250501 |
| eCl@ss 4.1 | 27250501 |
| eCl@ss 5.0 | 19030117 |
| eCl@ss 5.1 | 19030100 |
| eCl@ss 6.0 | 19170100 |
| eCl@ss 7.0 | 19170106 |
| eCl@ss 8.0 | 19170106 |
| eCl@ss 9.0 | 19170106 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000734 |
| ETIM 3.0 | EC000734 |
| ETIM 4.0 | EC000734 |
| ETIM 5.0 | EC000734 |
| ETIM 6.0 | EC000734 |
| ETIM 7.0 | EC000734 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 43172901 |
| UNSPSC 7.0901 | 43201404 |
| UNSPSC 11 | 43172015 |
| UNSPSC 12.01 | 43201410 |
| UNSPSC 13.2 | 43222612 |

Approvals

Approvals

Industrial Ethernet Switch - FL SWITCH SFN 5TX-24VAC - 2891021

Approvals

Approvals

UL Listed / cUL Listed / EAC / EAC / cULus Listed

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

| | | | |
|-----------|--|---|---------------|
| UL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 140324 |
|-----------|--|---|---------------|

| | | | |
|------------|--|---|---------------|
| cUL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 140324 |
|------------|--|---|---------------|

| | | | |
|-----|--|--|---------------|
| EAC | | | EAC-Zulassung |
|-----|--|--|---------------|

| | | | |
|-----|--|--|--------------------------|
| EAC | | | RU *- DE.A*30.B.01735 |
|-----|--|--|--------------------------|

| | | | |
|--------------|--|--|--|
| cULus Listed | | | |
|--------------|--|--|--|

Accessories

Accessories

End block

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

Patch cable

Industrial Ethernet Switch - FL SWITCH SFN 5TX-24VAC - 2891021

Accessories

Patch cable - FL CAT5 PATCH 0,3 - 2832250

Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263

Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276

Patch cable, CAT5, assembled, 1 m

Patch cable - FL CAT5 PATCH 1,5 - 2832221

Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289

Patch cable, CAT5, assembled, 2 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292

Patch cable, CAT5, assembled, 3 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580

Patch cable, CAT5, assembled, 5 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616

Patch cable, CAT5, assembled, 7.5 m

Patch cable - FL CAT5 PATCH 10,0 - 2832629

Patch cable, CAT5, assembled, 10 m

Industrial Ethernet Switch - FL SWITCH SFN 5TX-24VAC - 2891021

Accessories

Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

Safety locking

Port Guard Security Element - FL SEC PAC 4TX - 2832865



Layer1 security elements for four RJ45 network connections for use with patch boxes and panels
