

Datasheet

## RS Pro NPI52W Series Wire-wound SMD Inductor 220 $\mu$ H $\pm$ 20% Wire-Wound 2.4A Idc

RS Stock No: 740-9511



### Product Details

RS Pro wire-wound SMD inductor offers inductance of 220  $\mu$ H and withstands DC current up to 2.4 A. It works with DC-DC converters. This compact filter is suitable for both flow and reflow soldering.

### Features and Benefits

- High current (up to 8.6 Amps)
- Compact design
- Surface mountable construction
- High inductance (up to 1000  $\mu$ h)

**Specifications:**

Inductor Construction	Wire Wound
Shielded	No
Depth	15 mm
Dimensions	18.4 x 15 x 7 mm
Height	7 mm
Length	18.4 mm
Maximum DC Current	2.4 A
Maximum DC Resistance	380 mΩ
Maximum Operating Temperature	+85°C
Maximum Self Resonant Frequency	3.7 MHz
Minimum Operating Temperature	-40°C
Tolerance	±20%
Inductance	220 μH
Package/Case	52
Package Type	Tape & Reel