


# STANLEY

## STANLEY 300 mm Heavy Duty Hacksaw

1-20-110



### Features:

- 2 blade positions: 90° and 45°
- 136 kg permanent blade tension – faster cutting
- Patented quick blade change and lever to change tension suitable for application
- Bi-material ergonomic frame and handle for superior comfort and grip
- Easy tension memorisation and adjustment using a tightening wheel
- Steel frame for long life
- Locking and unlocking of the blade by a patented lever

### Description:

The STANLEY 300 mm Heavy Duty Hacksaw with 24 tpi has been designed for fine cutting of metal. The heavy duty hacksaw is capable of cutting both at 90° and 45°. The patented quick blade change lever system makes changing blades easy and convenient. The bi material ergonomic frame and handle offer enhanced comfort and grip during cutting application.

Specifications	
Length	300 mm
Teeth	24 TPI
Handle Material	Bi-Material
Blade material	Bi-Metal
Application	Metal