






(D)



TERMINAL CALL-OUTS MAY ALSO BE LISTED NUMERICALLY

3 - M4 X 4.9 mm
TERMINAL SCREW AND
INTERNAL TOOTHED
LOCK WASHER




RECOMMENDED MOUNTING:

M4 FASTENER WITH 6.00 IN.-LB [7.00 N-GF-CM] OF TORQUE MAX.

CHARACTERISTICS	
ELECTRICAL RATING	15A 250VAC (cULus) T55°C 15A 250V- (VDE) ST40
TERMINAL	SCREW
OPER. FORCE MAX	350 GMS
RELEASE FORCE MIN.	114 GMS
PRETRAVEL MAX.	.016 [0.4 mm]
OVERTRAVEL MIN.	.063 [1.6 mm]
MOVE. DIFF. MAX.	.002 [0.05 mm]
OPERATING POSITION	.826 TO .866 [21.0 TO 22.0 mm]

DWN: JED
APVD: SB
DATE: 25-May-04



CONFIDENTIAL AND PROPRIETARY:
ALL INFORMATION OR INVENTIONS CONTAINED IN THIS
DOCUMENT OR DERIVED FROM THE INFORMATION
HEREIN IS OWNED BY ZF ELECTRONICS CORPORATION,
AND IS CONFIDENTIAL AND PROPRIETARY. REVIEW OR
POSSESSION OF THIS DOCUMENT INDICATES AGREEMENT
THAT SUCH INFORMATION AND INVENTIONS WILL NOT BE
DISCLOSED, REPRODUCED OR OTHERWISE USED IN ANY
MANNER WITHOUT EXPRESS WRITTEN PERMISSION FROM AN
AUTHORIZED REPRESENTATIVE OF ZF ELECTRONICS
CORPORATION.



11200 80th AVE., PLEASANT PRAIRIE, WI 53158

NAME / DESCRIPTION

SWITCH

D	21540	10-Jul-12	AMH	EL
REV	ECO NO.	DATE	PREP	APVD

PROJECT	CSR
12-0087	

DWG UNITS	X.XX	X.XXX	ANGLES
INCHES	± 0.02	± 0.015	± 5.0 °

C	ITEM NO.	GPTCNC01
SCALE:	2:1	SH 1 OF 1

ORIGINAL OR PROJE