



Main

Range of product	Acti 9
Device short name	MINs
Product or component type	Silent electronic timer
Product compatibility	Mechanical compatibility with electrical comb bus-bars
Colour tint	White(RAL 9003)

Complementary

Device application	Building
Load type	Serial-corrected fluorescent tube, balast : conventional, (2300 VA) Parallel-corrected fluorescent tube, balast : conventional, (400 VA) Non-corrected fluorescent tube, balast : conventional, (2300 VA) Fluorescent tube, balast : electronic, (300 VA) Fluocompact lamp, balast : conventional, (1500 VA) Dual mounted fluorescent tube, balast : conventional, (2300 VA) 9 fluorescent lamp, balast : electronic, (7 W) 7 fluorescent lamp, balast : electronic, (23 W) 7 fluorescent lamp, balast : electronic, (20 W) 7 fluorescent lamp, balast : electronic, (15 W) 7 fluorescent lamp, balast : electronic, (11 W) 230 V AC incandescent lamp, (2300 W) 230 V AC halogen lamp, (2300 W)
Power consumption	<= 6 VA
Maximum switching current	16 A - 230 V AC pf = 1
[Ue] rated operational voltage	230 V (+10 % -15 %) AC 50/60 Hz
Time delay	Adjustable from 0.5 to 20 minutes
Mounting support	DIN rail
9 mm pitches	2
Connections - terminals	Screw terminals : <= 6 mm ²
Electrical insulation class	Class II
Width	18 mm
Height	89 mm
Depth	66 mm
Product weight	75 g

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP20 B

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0946 - Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - go to CaP for more details
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Available Download End Of Life Manual

Contractual warranty

Period	18 months
--------	-----------