



### Main

Range of product	TeSys D TeSys D control relay TeSys F
Product or component type	Auxiliary contact block
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NO + 2 NC
Connections - terminals	Lugs-ring terminals

### Complementary

Mounting location	Front
[Ui] rated insulation voltage	600 V - certifications CSA 690 V - conforming to IEC 60947-5-1 600 V - certifications UL
[Ue] rated operational voltage	690 V AC 25...400 Hz
[Ith] conventional free air thermal current	10 A at ≤ 60 °C
Irms rated making capacity	250 A DC 140 A AC
Permissible short-time rating	140 A at -5...60 °C 100 ms 120 A at -5...60 °C 500 ms 100 A at -5...60 °C 1 s
Protection type	GG fuse ≤ 10 A rating according to operational current for Ue ≤ 690 V
Associated fuse rating	IEC 60947-5-1
Mechanical durability	30 Mcycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Non-overlap time	1.5 ms on energisation (no overlap between NC and NO contact) 1.5 ms on de-energisation (no overlap between NC and NO contact)
Overlap time	1.5 ms
Insulation resistance	> 10 MOhm
Product weight	0.05 kg

### Environment

Environmental characteristic	Normal environment
Standards	BS 4794 EN 60947-5-1 IEC 60947-5-1 NF C 63-140 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without derating in temperature

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0629 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Download Product Environmental</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Period	18 months
--------	-----------