




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

U1

REVISED PER ECO-11-005027

23MAR2011

RK

HMR

U2

DIM "A" MAX ADDED IN TOP VIEW


21-07-11

SP

RP

PART NUMBER BOX PACKAGING	PART NUMBER REEL PACKAGING	NO OF POS "n"	DIMENSION "A" MAX
7-215083-4	215083-4	4	8.6
7-215083-6	215083-6	6	11.1
7-215083-8	215083-8	8	13.6
8-215083-0	1-215083-0	10	16.2
8-215083-2	1-215083-2	12	18.7
8-215083-4	1-215083-4	14	21.3
8-215083-6	1-215083-6	16	23.8
8-215083-8	1-215083-8	18	26.3
9-215083-0	2-215083-0	20	28.9
9-215083-4	2-215083-4	24	34.0

DEREELING DIRECTION AND POSITION OF CONNECTORS



250 CONNECTORS PER BOX
BOX PACKAGING

2500 CONNECTORS PER REEL
REEL PACKAGING

--	GLASS FILLED POLYESTER (RED)	HOUSING	3
TIN OVER NICKEL PLATING	PHOPHOR BRONZE	MALE CONTACT	2
--	GLASS FILLED POLYESTER (RED)	COVER	1
FINISH	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

P.V. Tongeren

CHK

H SPELDE 24-08-01

APVD

H SPELDE 24-08-01

PRODUCT SPEC

108-19052

APPLICATION SPEC

114-19016

WEIGHT

-

CUSTOMER DRAWING

TE

TE Connectivity

NAME

Micro-MaTch
MALE-ON-WIRE CONNECTOR

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-215083

RESTRICTED TO

-

SCALE 5:1

SHEET 1 OF 1

REV U2

NOTES:

1. SHOWN IS A 10 POSITION CONNECTOR

2. FOR FLAT RIBBON CABLE REQUIREMENTS.
SEE APPLICATION SPEC 114-19016.

3. CONNECTOR-HEIGHT AFTER CABLE TERMINATION 5.1 mm AVERAGE.
DEPENDING ON PROCESSING. SEE APPLICATION SPEC 114-19016.