








NOTES:

1. MATERIAL:

- ALL MATERIALS ARE RoHS COMPLIANT PER EU DIRECTIVE 2002/95/EC AND AMENDMENTS.
- OUTER SHELL - DIECAST ZINC ALLOY, NICKEL PLATED.
- CONTACTS - PHOSPHOR BRONZE, PLATED WITH 0.76 MICRONS (30 MICROINCHES) GOLD OVER 1.27 MICRONS (50 MICROINCHES) MINIMUM NICKEL ON THE MATING AREA WITH MATTE TIN OVER NICKEL ON THE TAILS.
- USB HOUSING - ENGINEERING THERMOPLASTIC, HIGH TEMPERATURE RESISTANT, FLAMMABILITY RATING UL94V-0 BLACK.
- USB SHIELD & BACK COVER - COPPER ALLOY, NICKEL PLATED.
- GASKET - SILICONE RUBBER, BLACK.
- PCB - FR-4 FIBERGLASS, LEAD FREE.
- CABLE HEADER: THERMOPLASTIC HOUSING (UL94V-0, BLACK) WITH BRASS CONTACTS (PLATED GOLD OVER NICKEL), TYCO P/N 5499786-2 OR EQUIVALENT. HEADER MATES WITH TYCO RECEPTACLE 1658620-2 WITH STRAIN RELIEF 499252-9 OR EQUIVALENT.
- DUST COVER - SILICONE RUBBER WITH NICKEL PLATED BRASS BUSHING. SEE ORDERING CODE FOR DUST COVER OPTIONS. SEE SHEET 2 FOR APPLICATION VIEW

2. ENVIRONMENTAL PERFORMANCE PER IEC 60529 CODE IP67 FOR SEAL BETWEEN MATING AREA AND PCB SIDE OF CONNECTOR. GASKET PROVIDES SEAL TO INSIDE FACE OF ENCLOSURE PANEL. AVAILABLE DUST COVER PROVIDES ADDED PROTECTION.

3. CURRENT RATING: 1.5 AMPERES

4. CONTACT RESISTANCE: 50 MILLIOHMS MAXIMUM (SUBJECT TO VERIFICATION)

5. OPERATING TEMPERATURE: -40 °C to +105 °C

6. DUST COVERS MAY BE ORDERED SEPARATELY, SPECIFY

- MUSB-2A111-014BP FOR GREY DUST COVER
- MUSB-2A111-024BP FOR BLACK DUST COVER

ORDERING CODE: **MUSB-A211-XX**

SERIES, RUGGED USB

USB SERIES 'A' RECEPTACLE, RIGHT ANGLE ON PCB WITH RIGHT ANGLE CABLE HEADER

THREAD OPTION

3 = #4-40 UNC THREAD

M = M3 x 0.5 THREAD

DUST COVER OPTION

0 = NO DUST COVER SUPPLIED

1 = WITH GREY DUST COVER SUPPLIED

5 = WITH BLACK DUST COVER SUPPLIED

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.


UNLESS SPECIFIED OTHERWISE	DRAWN	S.SEMENOV	MAR01/07
PRIMARY UNITS MILLIMETERS	CHECKED	K. LAMBIE	TBD
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.	A.GREEN	TBD
1 DECIMAL PLACE	ENG. REL. NO.	EAR 13560	
2 DECIMAL PLACES ±0.15	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION		
ANGULAR DEGREES			

Amphenol Canada Corp.


MUSB RUGGED SERIES A USB RECEPTACLE, RIGHT ANGLE, ON PCB WITH R/A CABLE HEADER, THREAD AND DUST COVER OPTIONS, RoHS COMPLIANT

P-MUSB-A211-XX



CODE ID NO. 03554 DWG SIZE: C SCALE: 3:1 SHEET 1 OF 2



RUGGED USB TO CABLE HEADER CONNECTION CHART	
RUGGED USB RECEPTACLE	CABLE HEADER
SHELL/GROUND	POSITION 1
CONTACT 1	POSITION 14
CONTACT 2	POSITION 13
CONTACT 3	POSITION 12
CONTACT 4	POSITION 11



RECOMMENDED PANEL CUTOUT
(OUTSIDE VIEW OF PANEL)




CONTACT 1 FOR
RUGGED USB

CONTACT 4 FOR
RUGGED USB

MUSB CONTACT ASSIGNMENT

MOUNTING SCREWS
(NOT SUPPLIED)

COVER HANDLE
WITH MARK "TOP"



ENCLOSURE PANEL

DUST COVER APPLICATION



UNLESS SPECIFIED OTHERWISE	DRAWN	S.SEMENOV	MAR01/07
PRIMARY UNITS MILLIMETERS	CHECKED	K.LAMBIE	TBD
SECONDARY UNITS INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.	A.GREEN	TBD
1 DECIMAL PLACE	ENG. REL. NO.	EAR 13560	
2 DECIMAL PLACES ±0.15	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION		
ANGULAR DEGREES	DO NOT SCALE DRAWING		

Amphenol Canada Corp.

MUSB RUGGED SERIES 'A' USB
RECEPTACLE, RIGHT ANGLE, ON PCB WITH
R/A CABLE HEADER, THREAD AND DUST
COVER OPTIONS, RoHS COMPLIANT

P-MUSB-A211-XX

DWG. NO.	REV
	D
CODE ID NO. 03554	DWG SIZE: C
SCALE: 3:1	SHEET 2 OF 2