



Datasheet


ENGLISH

New 5.08mm Plug 15A 2 way

RS Stock 874-5026



Dimensions: (mm)





Specifications

- Rating: 300V 15A
- Pitch:5.00mm
- Insulation Withstands Voltage: AC 2000V / Min
- Insulation Resistance: 500M or More at DC500V
- Using Temperature Range: -40 ~ +105
- Screw Torque Value: 4 kgf – cm (Max)
- Suitable Electric Wire: AWG ~ 12
- Un-Dimensional Tolerances: (see below)

—	∩	∇	0.05/10
⊥	//	≡	0.2/10
PITCH ERROR			0.05/10
UNDIMENSIONED TOLERANCES			±0.3

Materials

- Top Housing: Green PA66(VO)
- Wire Cage: Steel
- Screw: Steel
- Clamp: Bronze
- Base Housing: PA66 (VO)

P	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
U	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00	70.00	75.00
V	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00	70.00	75.00	80.00
P	17	18	19	20	21	22	23	24							
U	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00							
V	85.00	90.00	95.00	100.00	105.00	110.00	115.00	120.00							
Tolerances for PITCH ERROR															