

Datasheet

RS Pro Round Anti-Vibration Mount, 46mm, Vulcanised Rubber, Galvanised Steel 40daN, M10

RS Stock No: **442-684**



Product Details

RS Pro round anti-vibration mount has vulcanised rubber and galvanised steel construction for long life durability. It has a static load capacity of 40 kg and thread size of M10. A series of machine mount specially developed for lighter equipment such as wood processing machines, compactors, light industrial machinery, office equipment and domestic appliances. This light duty mounts consist of levelling bolts with vulcanised rubber feet which guarantees safe and reliable installation on most surfaces. This mount can be fitted both in internal and external holes in the machine frame and chassis.

Features and Benefits

- Withstands lighter loads
- Wide range suitable for most applications
- This light duty mounts consist of levelling bolts with vulcanised rubber feet which guarantees safe and reliable installation on most surfaces



ENGLISH

Specifications:

Foot Shape	Round
Material	Vulcanised Rubber
Metalwork	Galvanised Steel
Mounting Type	Screw-In
Type	Male Buffer Foot
Diameter	46 mm
Overall Height	53 mm
Static Load Capacity	40 kg
Thread Size	M10