


SPECIFICATION CONTROL DRAWING



Product Name	Product Dimensions					Wire Dimensions			
	øA min	B nom	C nom	L max	Color (1)	Size Range mm ² (AWG)	øG		
							min	max	
DP-2-63	4.0 [0.160]	6.35 [0.250]	0.8 [0.030]	30.0 [1.180]	Red	0.5 - 1.0 (AWG 22-18)	1.4 [0.055]	4.0 [0.160]	
DP-6-63	4.6 [0.180]	6.35 [0.250]	0.8 [0.030]	32.0 [1.260]	Blue	1.5 - 2.5 (AWG 16-14)	2.0 [0.080]	4.6 [0.180]	
DP-2-28	4.0 [0.160]	2.80 [0.110]	0.5 [0.020]	22.5 [0.885]	Red	0.5 - 1.0 (AWG 22-18)	1.4 [0.055]	4.0 [0.160]	


MATERIALS

1. INSULATION SLEEVE: Heat-shrinkable, transparent color (1), radiation cross-linked modified polyamide with thermoplastic adhesive coating inside.
2. PUSH-ON TERMINAL: Tin-plated brass.
BASE METAL: C260 Brass.
PLATING: Tin-plated per ASTM B545, Class A.

APPLICATION

1. These controlled crimp devices are designed to terminate a tin plated or bare copper stranded wire having an insulation rated for at least 85°C to a push-on terminal. It will provide a splash proof and strain relief connection.
UL listed wire connector 3Z11.
2. Temperature range: -55°C to +125°C.
3. For application tooling and installation, see RPIP-684-00.

For best results, prepare the wire as shown:



DuraSeal is a trademark of Tyco Electronics Corporation.

tyco Electronics		Tyco Electronics Corporation 300 Constitution Drive, Menlo Park, CA. 94025, U.S.A.		<i>Raychem</i>		TITLE: DURASEAL PUSH-ON RECEPTACLE			
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]					DOCUMENT NO.: DP-2-63/DP-6-63/DP-2-28				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A		ANGLES: N/A ROUGHNESS IN MICRON		Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.			REV.: A		DATE: 17-Jul-06
DRAWN BY: M. FORONDA		CAGE CODE: 06090	REPLACES: D030198	DCR NUMBER: D060174	SCALE: ---		SIZE: A	SHEET: 1 of 1	