

## Diode block - EMG 45-DIO14M - 2950129

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Diode module, with 14 diodes, common anode, diode type 1N 4007


The illustration shows a combination of versions EMG 22-DIO 7 P, EMG 45-DIO14 P and EMG 90-DIO 32 P

### Why buy this product

- Electrical decoupling of messages in fault reporting systems
- Spark-suppression diodes for limiting surge voltages of inductive loads



### Key commercial data

Packing unit	5 pc
GTIN	 4 017918 083977
Weight per Piece (excluding packing)	88.16 g
Custom tariff number	85411000
Country of origin	Germany

### Technical data

#### Dimensions

Width	45 mm
Height	75 mm
Depth	55 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

#### General

Diode type	1 N 4007
Max. operating voltage	250 V AC

# Diode block - EMG 45-DIO14M - 2950129

## Technical data

### General

Peak reverse voltage per diode	1300 V
Reverse current per diode	5 $\mu$ A
Conducting state voltage per diode	approx. 0.8 V
Conducting state current per diode	0.7 A (with single load) 0.2 A (with simultaneous loads)
Surge voltage category	III, basic insulation (as per EN 50178)
Mounting position	any
Assembly instructions	In rows with zero spacing

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3
Connection method	Screw connection

## Classifications

### eCl@ss

eCl@ss 4.0	27250312
eCl@ss 4.1	27260801
eCl@ss 5.0	27260801
eCl@ss 5.1	27260801
eCl@ss 6.0	27242602
eCl@ss 7.0	27242602
eCl@ss 8.0	27242602

### ETIM

ETIM 2.0	EC001432
ETIM 3.0	EC001597
ETIM 4.0	EC001597
ETIM 5.0	EC001596

### UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008

# Diode block - EMG 45-DIO14M - 2950129

## Classifications

### UNSPSC

UNSPSC 13.2	39121008
-------------	----------

## Approvals

### Approvals

---

### Approvals

### GOST

---


### Ex Approvals

---

### Approvals submitted

---

## Approval details



## Accessories

### Accessories

Marking material - EMG-GKS 12 - 2947035



Equipment marker, width 12 mm

## Drawings

# Diode block - EMG 45-DIO14M - 2950129

Circuit diagram

