

WML 14 (38X19)R


Order No.: 0817552

The figure shows a version of the article



Cable marker label, Roll, white, Unlabeled, Can be labeled with:
Thermomark R, Thermomark X, Thermomark S, Mounting type:
Adhesive, Cable diameter: ≤ 14 mm, Lettering field: 38 mm x 19 mm

Commercial data

| | |
|--------------------------|--|
| EAN |  4 046356 125598 |
| Pack | 1 |
| Customs tariff | 39191080 |
| Gross weight in pieces | 968.30 g |
| Country of Origin | DE |
| Catalog page information | Page 160 (CL2-2011) |

Product notes

WEEE/RoHS-compliant since:
14/10/2005



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

| | |
|-----------------------|-----------------------------|
| Length (b) | 63.5 mm |
| Width (a) | 38.1 mm |
| Color | white |
| Base element material | Vinyl film |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |

| | |
|---|---|
| Ambient temperature (operation) | -50 °C ... 110 °C |
| Components | Silicone-free |
| Material | PVC |
| Number of individual labels | 1500 |
| Number of individual labels per row | 2 |
| RoHS compliant | Yes |
| Halogen-free | Yes |
| Silicone-free | Yes |
| Cadmium-free | Yes |
| Adhesive | Acrylic |
| Printability | Thermal transfer |
| Device | 5146477 THERMOMARK ROLL |
| | 5145313 THERMOMARK S1 |
| | 5146257 THERMOMARK S1.1 |
| | 5145274 THERMOMARK X1.1 |
| | 5146231 THERMOMARK X1.2 |
| Ink ribbon | 5145384 THERMOMARK-RIBBON 110 |
| | 0829544 THERMOMARK-RIBBON 110 BU |
| | 0829542 THERMOMARK-RIBBON 110 GN |
| | 0829543 THERMOMARK-RIBBON 110 RD |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2006-02 + A1:2009-07 |
| Test duration | 96 h |
| Wipe resistance test result | Test passed |
| Salt spray test specification | DIN EN ISO 9227:2012-09 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Alternating condensation climate with SO2 test specification | DIN 50018:1997-06 |
| Climate level | KFW 1.0 S |
| Cycles | 2 |
| Condensation test result | Test passed |
| Burning behaviour | self-extinguishing |
| Foil strength | 0.06 mm |

Certificates

Certification

Certifications applied for:

Certification Ex:

Accessories

| Item | Designation | Description |
|------|-------------|-------------|
|------|-------------|-------------|

General

| | | |
|---------|-----------------------|--|
| 5145384 | THERMOMARK-RIBBON 110 | Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black |
|---------|-----------------------|--|

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG, England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;