

Northbrook, Illinois
Melville, New York • (831) 211-
Santa Clara, California • (408) 985-2400
Research Triangle Park,
North Carolina • (919) 549-1400
Camas, Washington • (360) 817-5500



LITTELFUSE INC
MR W TRAVIS, STANDARDS ENGINEER
800 E NORTHWEST HWY
DES PLAINES IL 60016

RE: Project Number(s) - 00NB

Your most recent listing is shown below. Please review this information and report any inaccuracies to the UL Engineering staff member who handled your project.

For information on placing an order for UL Listing Cards in a 3 x 5 inch format, please refer to the enclosed ordering information.

JDYX2
Fuses, Miscellaneous, Miniature, and Micro - Component

October 23, 2000

LITTELFUSE INC
800 E NORTHWEST HWY, DES PLAINES IL 60016

E10480

With pigtail leads

Micro, Cat. Nos. 262*, 268*, 272*, 273*, 276*, 279* followed by three digit decimal suffix 002 to 999 incl. or suffix 01.5, 0.002-5 amps, 125 v, ac or dc.

Cat. Nos. 251*, 252*, 255*, 256*, 265*, 266*, 275*, 276*, 491* followed by three digit decimal suffix 062 to 010 incl., rated 0.0625-10 amps 125 v, ac or dc; Cat. No. 250041, rated 10 amp, 125 v, ac or dc; Cat. No. 250034, 5 amp, rated 125 v, ac or dc; Cat. No. 491* followed by 062, rated 0.062 amps, 250 v, ac; Cat. No. 263* followed by 062 to 005 incl., rated 0.062-5 amps, 250 v, ac; Cat. No. 250038*, -099, 7-10 amps, rated 125 v, ac or dc.

Cat. Nos. 251*, 252*, 255*, 256*, 265*, 266*, 275*, 276*, 491* followed by three digit decimal suffix 012 to 015 incl., rated 12-15 amps, 32 v, ac or dc.

Cat. No. 270* followed by suffix Nos. 160 to 175 incl., rated 0.062-10 amps 125 v, dc.

Cat. Nos. 270186, 270187, rated 0.35 amp, 600 v, dc.

Cat. No. 433*, rated 0.25-0.375 amps, 125v ac/dc, rated 0.5-2.0 amps, 63 v ac/dc, rated 2.5-3A, 32V ac/dc.

Cat. Nos. 473*, 474* rated 0-7.0 amps 125 v, ac or dc.

Cat. No. 471* rated 0.5-5 amps, 125 v, ac or dc.

Miniature, Cat. Nos. 313*, 315*, F02B, 313ID* followed by 010 to 030 incl., rated 10-30 amps, 32 v, ac.

Series 221* followed by 050 to 010 incl., rated 0.50-10 amps, 250 v, ac.

Cat. Nos. 270154, 270161, rated 0.350 amp, 600 v, dc.

Cat. No. 230* followed by 004 to 007 incl., rated 4-7 amps, 125 v, ac/dc; Cat. No. WP90904 followed by 111 to 113 incl.; Cat. No. 220038, rated 5 amps, 250 v, ac, 125 v, dc.

Cat. No. 228* followed by 0032 to 10 incl., rated 0.032-10 amps, 250 v, ac.

Cat. No. 324* followed by 020; Cat. No. WP91768 followed by List 17, rated 300 v, ac, 125 v, dc; Cat. No. 324* followed by 025 or 030; Cat. No. WP91768 followed by List 18 or 19, rated 250 v, ac, 125 v, dc.

Cat. No. 325* followed by 012 to 030 incl.; Cat. No. WP91769 followed by List 35 to 39 incl., rated 12 to 20 amps, 250 v, ac, 25 to 30 amps, 125 v, ac.

Series 223* followed by 0.2 to 005 incl., rated 0.2-5 amps, 250 v, ac.

Series 227* followed by .032 through 005, rated 0.032-6.3A, 250 v, ac.

Series 2206* followed by 750-003, rated 0.75-3A, 125/300 v, ac.

Series 2205* followed by 250-02.5, rated 0.25-2.5A, 125/250 v, ac.

Cat. Nos. 220007*, -012*, -013*, -019*, -044*.

For PC board mount.

Micro, Cat. No. 202* followed by three digit decimal suffix 0.063 to 005 incl., rated 0.063-5 amps, 250 v, ac; Cat. No. 203* followed by three digit decimal suffix 0.250 to 005 incl., rated 0.25-5 amps, 250 v, ac.

For surface mount.

Micro, Cat. No. 271* followed by three digit decimal suffix 062 to 015 incl., rated 0.062-0.5 amps, 125 v, ac or dc, 0.75-4 amps, 60 v, ac or dc, 5-15 amps, 32 v, ac or dc.

Series 434*, 494*, 4000004 rated .5 amps 32V ac or dc, 4000005 rated 2 amps 32V ac or dc followed by .025 to 5 incl., rated .025-5 amps, 32 v, ac or dc.

Series 451*, 453* followed by 062 to 10 incl., rated 0.062-10 amps, 125 v, ac or dc maximum.

Underwriters Laboratories Inc. ®

Series 451*, 453* followed by 012 to 015 incl., rated 12-15 amps, 63 v, ac or dc; Series 452*, 454* followed by 375 to 005 incl., rated 0.375, .5 amps, 125 v, ac or dc.

Series 429* followed by 0.125 to 008 incl., rated 1/8-3/8 amp, 125 v, ac or dc; 1/2-2 amps, 63 v, ac or dc; 2-1/2-3 amps, 32 v, ac or dc; 4-8 amps, 24 v ac or dc. Series 430*, rated 0.5-2 amps, 63 v ac/dc; 3 amps, 32 v, ac; Series 431* followed by 0.25 to 003 incl., rated 0.25-5 amp, 32 v, ac or dc; Series 439* followed by 0.250 to 003 incl., rated 1/4-1/2 amp, 63 v, ac or dc; 3/4-3 amp, 32 v, ac or dc.

Cat. No. 450002*, rated 500 amps; Cat. No. 450007, rated 4 amp.; Cat. No. 450003, rated 3 amps.

Cat. Nos. 420001*, rated 1A; Cat. No. 420002*, rated 1.5A; Cat. No. 420003*, rated 2A; Cat. No. 420004*, rated 2.5A; Cat. No. 420005*, rated 3A; Cat. No. 420006*, rated 3.5A; Cat. No. 420007*, rated 4A; Cat. No. 420008*, rated 5A all rated 250 v, ac.

Cat. No. 459*, rated 0.062-5 amps, 125 v, ac or dc; Cat. No. 460*, 0.375-5 amps, 125 v, ac or dc.

Series 436* followed by 0.75 to 1.6 incl., rated 0.75-1.6 amp, 250 v ac.

For use with fuse holders.

Miniature, Cat. No. 301* followed by 002 to 010 incl., rated 2-10 amps, 32 v, ac.

Cat. No. 326* followed by 012, 015, 020, rated 12-20 amps, 250 v, ac, followed by 025, 030, rated 25-30 amp, 125 v, ac, Cat. No. WP91769 followed by 135 to 139 incl., rated 12-20 amp, 250 v, ac, 25-30 amp, 125 v, ac.

Series 213* followed by 0.2 to 6.3 incl., rated 0.2- 6.3 amps, 250 v, ac.

Cat. Nos. 216*, 226*, 616 followed by 0.050 to 10 incl., 0.05-10 amp, 250 v, ac.

Series 218* followed by 0.032 to 10 incl., rated 0.032-10 amp, 250 v, ac.

Series 219* followed by suffix numbers 8 through 06.3, rated 0.8-6.3 amp, 250 v, ac.

Series 217*, 617* followed by 0.032 through 008, rated 0.032-6.3 amp, 250 v, ac.

Series 618* followed by 0.032 through 6.3, rated 0.032 -6.3 amps, 250 v, ac.

Cat. Nos. 322001* to 322080* incl., WP92458 followed by List 1-16.

Cat. No. 220* followed by 015; Cat. Nos. 220021, -022, 4-7 amps, 125 v, ac

Cat. No. 229* followed by 004 to 007 incl., 4-7 amps, 125 v, ac; Cat. No. WP90904 followed by List 11 to 13 incl.

Series 215* followed by 0.50-010 incl., 0.50-10 amps, 250 v, ac.

Cat. No. 314* followed by 020; Cat. No. WP91768 followed by List 117, rated 300 Vac, 125 v, dc; Cat. No. 314* followed by 025 or 030; Cat. No. WP91768 followed by List 118 or 119, rated 250 Vac, 125 Vdc.

Cat. No. 220037, rated 0.75A, 300 v, ac; Cat. No. 220045, rated 2.0 amps, 350 v, ac, 125 v, dc.

Cat. No. 3100336 rated 300 v, ac, 125 v dc.

Miscellaneous, Cat. No. 511* followed by 010, 015, 020, 025, 030, 035, 040, 050, 060, 10-60 amps, 32 v, ac.

Cat. No. 585015* followed by 015, 15 amps, 1000 v, ac or dc; Cat. No. FLU 011, 1000 v, ac or dc.

Cat. No. 586001* followed by 001, 1 amps, 1000 v, ac or dc; Cat. No. FLU 440, 1000 v, ac or dc, -11A.

Micro, enclosed, nonrenewables, Type 662 or 663 followed by -.040, -.050, -.063, -.080, -.100, -.125, -.160, -.200, -.250, -.315, -.400, -.500, -.630, -.800, -.001, -.125, -.016, -.002, -.025, -.315, -.004, -.005 followed by -HXLL, -HXSL or -ZRL.

Type 66306.3 followed by -HXLL, -HXSL or -ZRL.

Type 664 followed by -.800, -.001, -.125, -.016, -.002, -.025, -.315, -.004, -.005, -.63 followed by -HXLL, -HXSL or -ZRL.

*With or without one prefix character and with or without additional suffix characters that signify options that do not affect the electrical characteristics.

Marking: Company name or "LF" and catalog designation on carton.

See General Information Preceding These Recognitions

For use only in equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.