

## Cable housing - KGG-MC 1,5/ 2 - 1834343

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable housing, Pitch: 3.81 mm, Number of positions: 2, Dimension a: 10.01 mm, Color: green

### Why buy this product

- ✓ For MC or IMC plugs with and without flange, and 3.81 mm pitch
- ✓ Straight cable outlet for sequencing several cable housings
- ✓ Incl. cable binders and marker strips for any numbers of positions
- ✓ Easier plug-in and disconnection processes
- ✓ Incl. transparent label carriers from 6- to 16-pos.
- ✓ Strain relief for the cables provided by cable binder or a clamp
- ✓ Full latching of both half shells of the cable housing



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 051860
Weight per Piece (excluding packing)	2.7 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Pitch	3.81 mm
Dimension a	10.01 mm

#### General

Range of articles	KGG-MC 1,5
Insulating material group	I
Insulating material	ABS
Flammability rating according to UL 94	HB

# Cable housing - KGG-MC 1,5/ 2 - 1834343

## Technical data

### General

Number of positions	2
---------------------	---

### Standards and Regulations

Flammability rating according to UL 94	HB
--	----

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440202

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000879
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

#### Approvals submitted

---

## Cable housing - KGG-MC 1,5/ 2 - 1834343

### Approvals

#### Approval details

EAC

### Drawings

Dimensional drawing

