

Product Information



LINEA

5940UAP100P30-13

EAN 4031582338713

Swivel castor, housing made of Polyamide, precision ball bearing in swivel head. Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing, bolt hole

Technical Data	
Wheel diameter	100 mm
Width of Tread	20 mm
Castor width	82 mm
Centre hole	13 mm
Dome-Ø	52 mm
Offset	32 mm
Swivel Interference	164 mm
Overall height	119 mm
Temperature	- 10 / + 40 °C
Standard	EN 12530
Weight	0.618 kg
Load capacity	100 kg
Load capacity (static)	200 kg
Swivel Radius	82 mm
Hardness of tread	A 92 Shore



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

Product Information



LINEA

5940UAP100P30-13

EAN 4031582338713

