

			DESIGNED FOR USE WITH .141 SR CABLE		REVISIONS																																																
			CABLE ENTRY DIAMETER MINIMUM		REV	DESCRIPTION	DATE	APPROVED																																													
			HOUSING .144 (3.66)		05 ₁	SEE GEN ECN 80-0084	T.M.C. 3-11-82	G.M. 3-11-82																																													
			CONTACT .037 (0.94)		05 ₂	UPDATED AND REDRAWN IN CAD PER ECN 88-0678; ADDED ELECTRICAL MECHANICAL AND ENV. SPEC BLOCK PER ECN 90-0493	M.C. 4-24-91	<i>QRL</i> 4-24-91																																													
					05 ₃	SEE ECN 92-0289	<i>OGM</i> 5/15/92	<i>AK</i> 5/15/92																																													
			B		PER EC 0U20-0692-00		9/21/01	<i>C. Hwang</i> 9/21/01																																													
<table><tr><th>ELECTRICAL</th><th>MECHANICAL</th><th>ENVIRONMENTAL</th></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions MIL-STD-348A, Fig. 304.1</td><td>Temperature Rating -65°C TO +105°C</td></tr><tr><td>Frequency Range (GHz) DC to 18</td><td>Recommended Mating</td><td>Vibration MIL-STD-1344, Method 2005, Condition IV, 30g Peak.</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level 500</td><td>Torque 12-15 LBS</td><td>Shock MIL-STD-1344, Method 2004, Condition G</td></tr><tr><td>VSWR 1.06 + .007 f(GHz)</td><td>Force to Engage and Disengage (In/Lbs MAX) 6.0</td><td>Thermal Shock MIL-STD-1344, Method 1003, Condition A, Except High Temp 115°C</td></tr><tr><td>Insertion Loss (dB MAX) .05 √f(GHz)</td><td>Cable Retention</td><td>Humidity MIL-STD-1344, Method 1002.</td></tr><tr><td>RF Leakage (dB MIN) -90 @ 2-3 GHz</td><td>Axial Force (Lbs) 60</td><td>No measurements at high humidity.</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 375</td><td>Torque (In/Oz) 55</td><td>Insulation resistance shall be at least 200 megohms within 5 minutes after removal from humidity.</td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1,500</td><td>Weight (Grams) 20.6</td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX)</td><td></td><td></td></tr><tr><td>Center Contact 1.5</td><td></td><td></td></tr><tr><td>Outer Contact 2.0</td><td></td><td></td></tr><tr><td>Cable to Housing 2.0</td><td></td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 1,000</td><td></td><td></td></tr><tr><td>IR.(Megohms MIN) 5,000</td><td></td><td></td></tr></table>			ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 304.1	Temperature Rating -65°C TO +105°C	Frequency Range (GHz) DC to 18	Recommended Mating	Vibration MIL-STD-1344, Method 2005, Condition IV, 30g Peak.	Volt Rating (VRMS MAX) @ Sea Level 500	Torque 12-15 LBS	Shock MIL-STD-1344, Method 2004, Condition G	VSWR 1.06 + .007 f(GHz)	Force to Engage and Disengage (In/Lbs MAX) 6.0	Thermal Shock MIL-STD-1344, Method 1003, Condition A, Except High Temp 115°C	Insertion Loss (dB MAX) .05 √f(GHz)	Cable Retention	Humidity MIL-STD-1344, Method 1002.	RF Leakage (dB MIN) -90 @ 2-3 GHz	Axial Force (Lbs) 60	No measurements at high humidity.	Corona, 70,000 Ft (VRMS MIN) 375	Torque (In/Oz) 55	Insulation resistance shall be at least 200 megohms within 5 minutes after removal from humidity.	Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1,500	Weight (Grams) 20.6		Contact Resistance (Milliohms MAX)			Center Contact 1.5			Outer Contact 2.0			Cable to Housing 2.0			RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 1,000			IR.(Megohms MIN) 5,000			HOUSING COUPLING NUT DIELECTRIC CENTER CONTACT GASKET RETAINING RING		STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303 STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303 TFE FLUOROCARBON PER ASTM-D-1457 BRASS PER ASTM-B-16, HALF HARD SILICONE RUBBER PER ZZ-R-765 PHOSPHOR BRONZE PER QQ-B-750, GRADE B2		GOLD PLATE PER MIL-G-45204 PASSIVATE PER QQ-P-35 N/A GOLD PLATE PER MIL-G-45204 N/A N/A	
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																			
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 304.1	Temperature Rating -65°C TO +105°C																																																			
Frequency Range (GHz) DC to 18	Recommended Mating	Vibration MIL-STD-1344, Method 2005, Condition IV, 30g Peak.																																																			
Volt Rating (VRMS MAX) @ Sea Level 500	Torque 12-15 LBS	Shock MIL-STD-1344, Method 2004, Condition G																																																			
VSWR 1.06 + .007 f(GHz)	Force to Engage and Disengage (In/Lbs MAX) 6.0	Thermal Shock MIL-STD-1344, Method 1003, Condition A, Except High Temp 115°C																																																			
Insertion Loss (dB MAX) .05 √f(GHz)	Cable Retention	Humidity MIL-STD-1344, Method 1002.																																																			
RF Leakage (dB MIN) -90 @ 2-3 GHz	Axial Force (Lbs) 60	No measurements at high humidity.																																																			
Corona, 70,000 Ft (VRMS MIN) 375	Torque (In/Oz) 55	Insulation resistance shall be at least 200 megohms within 5 minutes after removal from humidity.																																																			
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1,500	Weight (Grams) 20.6																																																				
Contact Resistance (Milliohms MAX)																																																					
Center Contact 1.5																																																					
Outer Contact 2.0																																																					
Cable to Housing 2.0																																																					
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 1,000																																																					
IR.(Megohms MIN) 5,000																																																					
			COMPONENT	MATERIAL	FINISH																																																
			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	DRAWN BY DRB CHECKED BY EDT APPD BY D.NANIA	DATE 6-15-67 7-19-67 9-25-67	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																															
			These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE 408-04915 NO. AP. (30-001)		TITLE TYPE N STRAIGHT CABLE PLUG DIRECT SOLDER ATTACHMENT																																															
			.XXX = in XX.X = mm (REF)		SIZE B	CODE IDENT NO. 26805	3001-7941-00	REV 05 ₃																																													
					SCALE 4:1	SHEET 1 OF 1																																															

| CUSTOMER DRAWING | | | | | | AMP PART # 1057088-1 SHEET 1 OF 1 REV B | | |