

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ethernet Lean Managed Switch with four 10/100 Mbps RJ45 ports and two 10/100 Mbps FX-SC single-mode ports

Product description

The compact Lean Managed Switches (LM) enable the flexible and cost-effective creation of managed Ethernet networks in automation applications. Thanks to the wide range of connection versions and the extended temperature range of -40°C to +70°C, it optimally meets the requirements of industrial applications. It supports PROFINET conformance class C. And its integrated software enables the redundant creation, diagnostics, and monitoring of networks using IT standard protocols.

Why buy this product

- Web-based management, SNMP
- Compact housing
- Comprehensive fiber optic versions
- Configuration can be stored externally
- 40°C ... +70°C ambient temperature
- Configurable alarm contact



Key commercial data

Packing unit	1 pc
GTIN	
Weight per Piece (excluding packing)	307.3 g
Custom tariff number	85176200
Country of origin	Germany

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	45 mm
Height	99 mm

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Technical data

Dimensions

Depth	112 mm
-------	--------

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	30 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Air pressure (operation)	80 kPa ... 108 kPa (2000 above sea level)
Air pressure (storage/transport)	70 kPa ... 108 kPa (3000 above sea level)
Noise immunity	EN 61000-6-2:2005

Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	4 (RJ45 ports)
Connection method	RJ45
Note on connection method	Auto negotiation and autocrossing
Transmission physics	Copper
Transmission speed	10/100 MBit/s
Transmission length	100 m (per segment)
Interface 2	Ethernet FO
No. of ports	2 (SC single-mode)
Connection method	SC
Transmission physics	Single mode fiberglass
Transmission speed	100 MBit/s (full duplex)
Transmission length	36000 m (fiberglass with F-G 9/125 0.36 dB/km)
	32000 m (fiberglass with F-G 9/125 0.4 dB/km)
	26000 m (fiberglass with F-G 9/125 0.5 dB/km)
Wavelength	1300 nm
Interface 5	Serial (V.24 (RS-232))
Connection method	V.24 (RS-232-C), 6-pos. MINI-DIN socket (PS/2)

Function

Basic functions	Store-and-forward switch complies with IEEE 802.3 2, priority classes according to IEEE 802.1 P TCP/IP protocol, BootP-compatible, port mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), DHCP server, PTCP filter
Supported browsers	Internet Explorer 5.5 or higher
Redundancy	Rapid Spanning Tree 802.1w, Fast Ring Detection
Status and diagnostic indicators	Per Ethernet 2 status LEDs: LINK and status activity, 100, full duplex, supply voltage U_{S1} and U_{S2} (redundant supply voltage)

Network expansion parameters

Cascading depth	Network, linear, and star structure: any
-----------------	--

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Technical data

Network expansion parameters

Maximum conductor length ((twisted pair)	100 m
--	-------

Supply voltage

Supply voltage	24 V DC
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Supply voltage range	18.5 V DC ... 30.5 V DC
Typical current consumption	400 mA (at U _S = 24 V DC)

General

Mounting type	DIN rail
Type AX	Block design
Weight	230 g
Noise emission	EN 61000-6-3/-4

Mechanical tests

Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	Operation/Storage/Transport: 5 g, 150 Hz, Criterion 3

Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion B
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion B
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A

Classifications

eCl@ss

eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	27250501
eCl@ss 5.1	27250501
eCl@ss 6.0	19170106
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Classifications

ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410

Approvals

Approvals

Approvals

GL / BV / DNV / GL-SW / GL / BV / DNV / GL-SW / UL Listed / cUL Listed / GL / cULus Listed

Ex Approvals

Approvals submitted

Approval details

GL

BV

DNV

GL-SW

GL

BV

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Approvals

DNV

GL-SW

UL Listed

cUL Listed

GL

cULus Listed

Accessories

Accessories

Connector set

RJ45 connector - FL PLUG RJ45 GR/2 - 2744856

RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.



RJ45 connector - FL PLUG RJ45 GN/2 - 2744571

RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.



Data cable preassembled

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Accessories

Fiber optic cables - VS-PC-2XGOF-50-SCRJ/SCDU-1 - 1654400



Assembled fiber optic cable, break-out cable, fiberglass multi-mode 50/125 μm , SCRJ/IP20 on SC-duplex/IP20, for installation inside control cabinets, length: 1 m

FO patch cable - FL MM PATCH 1,0 LC-SC - 2989161



Assembled fiber optic cable, break-out cable, fiberglass multi-mode 50/125 μm , connector: LC/SC duplex, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 1 m

FO patch cable - FL MM PATCH 2,0 LC-SC - 2989268



Assembled fiber optic cable, break-out cable, fiberglass multi-mode 50/125 μm , connector: LC/SC duplex, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 2 m

FO patch cable - FL MM PATCH 5,0 LC-SC - 2901800



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , plug: LC / SC-Duplex, protection type: IP20, for installation in cable ducts or control cabinets, length: 5 m

FO patch cable - FL MM PATCH 1,0 SC-SC - 2901805



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , connector: SC Duplex / SC-Duplex, protection type: IP20, for installation in cable ducts or control cabinets, length: 1 m

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Accessories

FO patch cable - FL MM PATCH 2,0 SC-SC - 2901807



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , connector: SC Duplex / SC-Duplex, protection type: IP20, for installation in cable ducts or control cabinets, length: 2 m

FO patch cable - FL MM PATCH 5,0 SC-SC - 2901808



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , connector: SC Duplex / SC-Duplex, protection type: IP20, for installation in cable ducts or control cabinets, length: 5 m

FO patch cable - FL MM PATCH 1,0 SC-ST - 2901809



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , connector: SC Duplex / B-FOC, protection type: IP20, for installation in cable ducts or control cabinets, length: 1 m

FO patch cable - FL MM PATCH 2,0 SC-ST - 2901810



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , connector: SC Duplex / B-FOC (ST), protection type: IP20, for installation in cable ducts or control cabinets, length: 2 m

FO patch cable - FL MM PATCH 5,0 SC-ST - 2901811



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , connector: SC Duplex / B-FOC (ST), protection type: IP20, for installation in cable ducts or control cabinets, length: 5 m

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Accessories

FO patch cable - FL MM PATCH 1,0 SC-SCRJ - 2901812



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , connector: SC Duplex / B-FOC (ST), protection type: IP20, for installation in cable ducts or control cabinets, length: 1 m

FO patch cable - FL MM PATCH 2,0 SC-SCRJ - 2901813



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , connector: SC Duplex / SCRJ, protection type: IP20, for installation in cable ducts or control cabinets, length: 2 m[^]

FO patch cable - FL MM PATCH 5,0 SC-SCRJ - 2901814



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 μm , connector: SC Duplex / B-FOC (ST), protection type: IP20, for installation in cable ducts or control cabinets, length: 5 m

Drivers and interfaces

Software - FL SNMP OPC SERVER - 2832166



SNMP-OPC server, German and English, for monitoring and configuration of SNMP-capable equipment in HMI and SCADA systems

End block

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

Fiber optics connector (device side)

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Accessories

Fiber optic coupling - VS-SCRJ-GOF-KU - 1654358



SCRJ coupling insert, duplex, for VS-PP-19-1HE-16-F patch panel and VS-TO...F...terminal outlets and VS-SI-FP-2F front plate, can be used for glass multi-mode, HCS and polymer fiber types

Network management software

Software - FL SWT - 2831044



Factory Manager, multilingual, configuration and diagnostics software for ETHERNET networks in automation

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1.0 m

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Accessories

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2.0 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3.0 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5.0 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Accessories

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10.0 m

Patch cable - FL CAT6 PATCH 12,5 - 2891369



Patch cable, CAT6, pre-assembled, 12.5 m

Patch cable - FL CAT6 PATCH 15,0 - 2891372



Patch cable, CAT6, pre-assembled, 15.0 m

Patch cable - FL CAT6 PATCH 20,0 - 2891576



Patch cable, CAT6, pre-assembled, 20.0 m

Patch panel

Patch panels - FL PF 2TX CAT5E - 2891165



Patch field with two RJ45 CAT5e network connections

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX SM - 2891916

Accessories

Patch panels - FL PF 8TX CAT5E - 2891178



Patch field with eight RJ45 CAT5e network connections

Programming cable

Connecting cable - PRG CAB MINI DIN - 2730611



Connecting cable, for connecting the controller to a PC (RS-232) for PC Worx, 3 m in length

Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

Universal tools

Assembly tool - FL CRIMPTOOL - 2744869



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site

Software - IPASSIGN - 2701094



IPAssign is an easy to use tool for setting the IP address of devices which rely on BOOTP. No installation or administrative rights are required to use IPAssign. With a simple selection, you can filter out all of the devices except those from Phoenix Contact.
